

BALDOR®

Polishing Lathes and Accessories



Polishing Lathes have features preferred by Dentists, Dental Lab Technicians, Jewelers, Lapidary and others for precision, trouble free polishing.

Features and Benefits

- The motor construction is totally enclosed, non-ventilated, dust and splash proof
- Moisture resistant copper wire is used in the stator winding to provide longer life
- Two winding stator construction permits higher starting and running torques
- Dynamically balanced rotor and shaft provides vibration free, quiet operation
- Tapered shafts accommodate chucks with standard dental taper, (right side of #380WCT is equipped with the Wells "Super Quick" chuck and the #LPL50 and #LPL75 have 5/8 inch diameter straight shafts)
- The ball bearings are lubricated for life and sealed to prevent entry of dust and debris. The bearings never need re-lubrication
- 8 feet, 3 conductor cord with plug is standard, (#342 supplied with cord less plug)
- Rubber feet and heavy construction minimizes bench creep, provisions for mounting to the laboratory bench are provided
- Modern design with smooth surfaces for easy cleaning
- Shaft center heights of 4-11/16 inches, 5-1/4 inches and 8 inches offer a variety of convenient work heights
- Manual reset overload protects the lathe from excessive operating temperatures that may damage the lathe, (no overload on #340, #342, #LPL50 and #LPL75)
- Underwriters Laboratory file #E23045(R)
- Canadian Standards Association file #LR2262
- Full 3 year warranty

BALDOR... The Right Choice For Quality, and Service Since 1920

FULL 3 YEAR WARRANTY

ALL BALDOR POLISHING LATHES WARRANTED FOR 3 FULL YEARS!

Baldor polishing lathes are warranted against burnouts, defective materials and workmanship for three full years. Warranty covers all parts except those subject to normal wear. *Wells Quick Chuck warranted one year by manufacturer.

POLISHING LATHES

"SUPER-SAVER" POLISHING LATHES



340

Catalog No.	HP	No. of Speeds	RPM	Volts	Phase	Hz	Shpg. Wgt. lbs/kg	Length	Shaft Ctr. Ht.
340	1/4	2	3600/1800	115	1	60	31/14.6	13-1/8"	4-11/16"
342	1/4	2	3000/1500	220-240	1	50	31/14.6	13-1/8"	4-11/16"

Note: U.L. Component Recognition – File #E46145, C.S.A Certified, Tapered shafts accommodate chuck with standard dental taper.

POLISHING LATHES



353T

Catalog No.	HP	No. of Speeds	RPM	Volts	Phase	Hz	Shpg. Wgt. lbs/kg	Length	Shaft Ctr. Ht.
353T	1/4	2	3450/1725	115	1	60	35/15.9	14-1/4"	5-1/4"
359T	1/2	1	3450	115	1	60	36/16.3	14-1/4"	5-1/4"

Note: U.L. Listed, C.S.A Certified, Tapered shafts accommodate chuck with standard dental taper.

POLISHING LATHES

HEAVY DUTY LABORATORY LATHES



380WCT

Catalog No.	HP	No. of Speeds	RPM	Volts	Phase	Hz	Shpg. Wgt. lbs/kg	Length	Shaft Ctr. Ht.
380T	1/3	2	3450/1725	115	1	60	41/18.6	15-1/4"	5-1/4"
380WCT*	1/3	2	3450/1725	115	1	60	45/20.4	16-3/4"	5-1/4"

Note: U.L. Listed, Not C.S.A Certified

*Baldor 380WCT laboratory lathe with Wells "Quick Chuck"

Includes 2 mandrels, 2 stone, 1 arbor band and 1 soft wheel chuck.

HEAVY DUTY SINGLE SHAFT LATHES



LPL50

Catalog No.	HP	No. of Speeds	RPM	Volts	Phase	Hz	Shpg. Wgt. lbs/kg	Length	Shaft Ctr. Ht.
LPL50	1/2	1	3450	115	1	60	43/19.5	14-3/8"	8"
LPL75	3/4	1	3450	115/230	1	60	48/21.8	14-3/8"	8"

Note: U.L. Component Recognition - File #E46145, Not C.S.A Certified

Straight Shaft - 5/8" Diameter

CHUCKS for Polishing Lathes

Baldor True-Running Chucks

Made to close-tolerance specifications - keeps vibration to an absolute minimum. All chucks guaranteed to match Baldor lathes and other makes with standard tapered shafts.



R1 **R2** **L3** **L4** **R5A** **R6** **L7**
Hard Wheel **Soft Wheel** **Hard Wheel** **Soft Wheel** **Burr Chuck** **Arbor Band** **Burr Chuck**

Mounting Hole 0.370" Tapered at rate of 1/4" per foot.

TRUE-RUNNING CHUCKS

Catalog No.	Description	Shipping Weight	
		lbs	kg
R1①	Hard wheel, right hand, brass	0.1	0.05
R2	Soft wheel, right hand, brass	0.2	0.09
L3①	Hard wheel, left hand, brass	0.1	0.05
L4	Soft wheel, left hand, brass	0.2	0.09
R5A②	Burr chuck, right hand, stainless & brass	0.5	0.23
R6③	Arbor band, right hand, brass	0.2	0.09
L7②	Burr chuck, left hand, stainless & brass	0.5	0.23

Note: ①R & L3 hard wheel chucks accommodates up to 1/4" wide wheel with 1/4" arbor hole.

②R5A & L7 burr chucks accommodate up to 1/4" shank.

③R6 arbor band chuck accommodates 1/2" wide x 3/4" diameter arbor band.

DA-1	Dust Bag (Filter) for #D60 and # D61 Dust Collector	2/0.9
------	---	-------



UNITED STATES

ARIZONA

PHOENIX
4211 S 43RD PLACE
PHOENIX, AZ 85040
PHONE: 602-470-0407
FAX: 602-470-0464

CALIFORNIA

LOS ANGELES
6480 FLOTILLA
COMMERCE, CA 90040
PHONE: 323-724-6771
FAX: 323-721-5859

HAYWARD
21056 FORBES STREET
HAYWARD, CA 94545
PHONE: 510-785-9900
FAX: 510-785-9910

COLORADO

DENVER
2520 W BARBERRY PLACE
DENVER, CO 80204
PHONE: 303-623-0127
FAX: 303-595-3772

CONNECTICUT

WALLINGFORD
65 SOUTH TURNPIKE ROAD
WALLINGFORD, CT 06492
PHONE: 203-269-1354
FAX: 203-269-5485

FLORIDA

**TAMPA/PUERTO RICO/
VIRGIN ISLANDS**
3906 EAST 11TH AVENUE
TAMPA, FL 33605
PHONE: 813-248-5078
FAX: 813-247-2984

GEORGIA

ATLANTA
62 TECHNOLOGY DR.
ALPHARETTA, GA 30202
PHONE: 770-772-7000
FAX: 770-772-7200

ILLINOIS

CHICAGO
795 MITTEL DRIVE
WOOD DALE, IL 60191
PHONE: 630-787-9600
FAX: 630-787-0434

INDIANA

INDIANAPOLIS
5525 W. MINNESOTA STREET
INDIANAPOLIS, IN 46241
PHONE: 317-246-5100
FAX: 317-246-5110
800-428-4141

IOWA

DES MOINES
1901 BELL AVENUE, SUITE 7
DES MOINES, IA 50315
PHONE: 515-244-9996
FAX: 515-244-6124

MARYLAND

BALTIMORE
6660 SANTA BARBARA RD.
SUITE 22-24
ELKRIDGE, MD. 21075
PHONE: 410-579-2135
FAX: 410-579-2677

MASSACHUSETTS

BOSTON
317 BROOKS ST.
WORCESTER, MA 01606
PHONE: 508-854-0708
FAX: 508-854-0291

MICHIGAN

DETROIT
33782 STERLING PONDS BLVD.
STERLING HEIGHTS, MI 48312
PHONE: 810-978-9800
FAX: 810-978-9969

GRAND RAPIDS
668 3 MILE ROAD NW
GRAND RAPIDS, MI 49504
PHONE: 616-785-1784
FAX: 616-785-1788

MINNESOTA

MINNEAPOLIS
21080 134TH AVE. NORTH
ROGERS, MN 55374
PHONE: 763-428-3633
FAX: 763-428-4551

MISSOURI

ST LOUIS
422 INDUSTRIAL DRIVE
MARYLAND HEIGHTS, MO 63043
PHONE: 314-298-1800
FAX: 314-298-7660

MISSOURI (cont.)

KANSAS CITY
915 N W PLATTE VALLEY DR
RIVERSIDE, MO 64150
PHONE: 816-587-0272
FAX: 816-587-3735

NEW YORK

AUBURN
ONE ELLIS DRIVE
AUBURN, NY 13021
PHONE: 315-255-3403
FAX: 315-253-9923

NORTH CAROLINA

GREENSBORO
1220 ROTHERWOOD ROAD
GREENSBORO, NC 27406
P O BOX 16500
GREENSBORO, NC 27416
PHONE: 336-272-6104
FAX: 336-273-6628

OHIO

CINCINNATI
2900 EARHART COURT
SUITE 200
HEBRON, KY 41048
PHONE: 859-586-0222
FAX: 859-586-0779

CLEVELAND
8929 FREEWAY DRIVE
MACEDONIA, OH 44056
PHONE: 330-468-4777
FAX: 330-468-4778

OKLAHOMA

TULSA
2 EAST DAWES
BIXBY, OK 74008
PHONE: 918-366-9320
FAX: 918-366-9338

OREGON

PORTLAND
20393 SW AVERY COURT
TUALATIN, OR 97062
PHONE: 503-691-9010
FAX: 503-691-9012

PENNSYLVANIA

PHILADELPHIA
1035 THOMAS BUSCH
MEMORIAL HIGHWAY
PENNSAUKEN, NJ 08110
PHONE: 856-661-1442
FAX: 856-663-6363

PITTSBURGH

616H BEATTY ROAD
MONROEVILLE, PA 15146
PHONE: 412-380-7244
FAX: 412-380-7250

TENNESSEE

MEMPHIS
4000 WINCHESTER ROAD
MEMPHIS, TN 38118
PHONE: 901-365-2020
FAX: 901-365-3914

TEXAS

HOUSTON
4647 PINE TIMBERS
SUITE # 135
HOUSTON, TX 77041
PHONE: 713-895-7062
FAX: 713-690-4540

DALLAS

3040 QUEBEC
DALLAS, TX 75247
PHONE: 214-634-7271
FAX: 214-634-8874

ODESSA

6968 EAST COMMERCE
ODESSA, TX 79762
PHONE: 915-367-2707
FAX: 915-367-9877

UTAH

SALT LAKE CITY
70 WEST SENIOR WAY
SALT LAKE CITY, UT 84115
PHONE: 801-973-6363
FAX: 801-973-6301

WISCONSIN

MILWAUKEE
2725 SOUTH 163RD STREET
NEW BERLIN, WI 53151
PHONE: 262-784-5940
FAX: 262-784-1215

INTERNATIONAL SALES

FORT SMITH, AR
BALDOR ELECTRIC CO
FORT SMITH, AR 72902
PHONE: 479-646-4711
FAX: 479-648-5895

CANADA

EDMONTON, ALBERTA
4053-92 STREET
EDMONTON, ALBERTA T6E6R8
PHONE: 780-434-4900
FAX: 780-438-2600

OAKVILLE, ONTARIO

2750 COVENTRY ROAD
OAKVILLE, ONTARIO L6H6R1
PHONE: 905-829-3301
FAX: 905-829-3302

MONTREAL, QUEBEC

1844 WILLIAM STREET
MONTREAL, QUEBEC H3J1R5
PHONE: 514-933-2711
FAX: 514-933-8639

VANCOUVER,

BRITISH COLUMBIA
1538 KEBET WAY
PORT COQUITLAM, BC V3C 5M5
PHONE 604-421-2822
FAX: 604-421-3113

WINNIPEG, MANITOBA

54 PRINCESS STREET
WINNIPEG, MANITOBA R3B1K2
PHONE: 204-942-5205
FAX: 204-956-4251

AUSTRALIA

UNIT 3, 6 STANTON ROAD
SEVEN HILLS, NSW 2147,
AUSTRALIA
PHONE: (61) (2) 9674 5455
FAX: (61) (2) 9674 2495

UNIT 3-73 MAIN ROAD

CLAYTON VIC 3168,
AUSTRALIA
PHONE: (61) (3) 5624555
FAX: (61) (3) 5624822

CHINA

SHANGHAI JIAHUA BUSINESS CENTER
ROOM NO. C-203
808 HONG QIAO ROAD
SHANGHAI 200021
PHONE: 86-21-64473060
FAX: 86-21-64078620

EL SALVADOR

BALDOR CENTROAMERICA
RESIDENCIAL PINARES DE SUIZA
POL. 15 #44, NVA. SAN SALVADOR
EL SALVADOR, CENTRO AMERICA
PHONE: (503) 288-1519
FAX: (503) 288-1518

FRANCE

2, RUE DU VALLON
94440 MAROLLES EN BRIE
PHONE: 33 145 10 7902
FAX: 33 145 99 0864

GERMANY

DIESELSTRASSE 22
D-85551 KIRCHHEIM
MUNICH, GERMANY
PHONE: (49) (89) 90508 - 0
FAX: (49) (89) 90508 - 491

ITALY

VIA G. GALILEI, 17
22070 GUANZATE (CO) ITALIA
PHONE: 39 031 35 29 174
FAX: 39 031 35 29 126

JAPAN

NEO MIME 501
2-5 DAIMACHI,
KANAGAWA-KU
YOKOHAMA, 221-0834,
JAPAN
PHONE: 81-45-412-4506
FAX: 81-45-412-4507

MÉXICO

BLVD. AL AEROPUERTO, KM. 2
LEÓN 37545, GUANAJUATO,
MÉXICO
PHONE: 52-477-761-2030
FAX: 52-477-761-2010

PANAMA

BALDOR SUDAMERICA
9109 0818, ZONA 6 BETHANIA
PANAMA CITY, REP. DE PANAMA
PHONE: (507) 261-5347
FAX: (507) 261-5355

PHILIPPINES

ROOM 604, WEB-JET ACROPOLIS BLDG.
8120 E. RODRIGUEZ AVENUE
BAGUMBAYAN, QUEZON CITY
PHILIPPINES
PHONE: (632) 638-2241
FAX: (632) 638-2242

SINGAPORE

51 KAKI BUKIT ROAD 2
K B WAREHOUSE COMPLEX
SINGAPORE 417863
PHONE: (65) 6 744 2572
FAX: (65) 6 747 1708

SWITZERLAND

POSTFACH 73
SCHUTZENSTRASSE 59
CH-8245 FEUERTHALEN
SWITZERLAND
PHONE: (41) (52) 6474700
FAX: (41) (52) 6592394

TAIWAN

ROOM R, 2F, NO. 124
CHUNG CHENG ROAD, SHIHLIN DIST.
TAIPEI 11141
PHONE: 886-2-2835-1666 EXT. 802
FAX: 886-2-2835-1717

UNITED KINGDOM

6 BRISTOL DISTRIBUTION PARK
HAWLKEY DRIVE
BRISTOL BS32 0BF U.K.
PHONE: 44 1454 850000
FAX: 44 1454 859001



P.O. Box 2400 • Fort Smith, AR 72902-2400 U.S.A.

Ph: (479) 646-4711 • Fax (479) 648-5792

International Fax (479) 648-5895

www.baldor.com