ABB BALDOR RELIANCE

Customer information packet

111

20C 2P BUFFER

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/19/2026 11:43:37 AM

Part Detail

Revision	N
Type	AC
Mech. spec.	G7-0429
Base	
Status	PRD/A
Elec. spec.	G7WG0030
Layout	G7LY0429
Eff. date	10-06-2026
CD Diagram	CD0279
Poles	02
Leads	4#18
Proprietary	False
Created date	08-06-2018


Nameplate


NP3352L				
CAT.NO.	111			
HP	.33	**VOLTS**	115	
PHASE	1	**AMPS**	4.2	
HZ	60	**RPM**	3600	
SER.NO				
SPEC.	G7-0429-0030G1			
BLANK				

Accessories

Part number	Description	Multiplier
GA16E	PEDESTAL LIGHT INDUSTRIAL,STEEL	A8
GA16	PEDESTAL INDUSTRIAL, CAST IRON 6" - 10"	A8
GA14	PEDESTAL FABRICATED STEEL W/SHELVES	A8
A65	6" COTTON BUFFING WHEEL 1/2" BORE	A8
BQ1-015-CC	1PH Brake, NEMA 1,110-125 VAC, 50/60Hz	P1
BQ1-015-CP	1PH Brake, Panel 110-125 VAC, 50/60 Hz	

G7LY0429





G7LY0429

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.

REV. DESC: NEW		
REV. LTR: –	VERSION: 00	TDR: 000001079698
FILE: \AAA\00244\395	REVISED: 04:31:41 08/06/2018	BY: ENMARH0
MTL: –		


BALDOR - RELIANCE®

BUFFER 7" TYPE"C"–115V W/SHAFT EXT FROM G6–209 (.50 DIA)


SH 1 of 1


CD0279

MOTOR




BASE





	S1	S4	JOIN
HIGH	1,P1	4	2,3,P2
LOW	1,3,P1	2,4,P2	–



NOTES:

1. CONNECTIONS ARE SHOWN FOR CW ROTATION FACING END OPPOSITE SHAFT EXTENSION (OPP STD). FOR CCW ROTATION, INTERCHANGE (5) AND (8) INTERNALLY.
2. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: ADDED ANTI–ROTATION DETAIL TO RH SIDE OF SWITCH		
REV. LTR: E	VERSION: 01	TDR: 000000863536
FILE: \AAA\00028\193	REVISED: 09:52:27 07/23/2014	BY: ENCHALO
MTL: –		

BALDOR

TYPE C, DV, FIX, OPT. LIGHTED EYESHIELD, GRINDER

SH 1 of 1

CD0279