





NOTE:

1. SHAFT RUNOUT ON BOTH ENDS
(2.25" FROM END OF SHAFT)
MUST BE .002 MAX. T.I.R.



CUST. NAME		CUST. P.O.		CERTIFIED BY		MODEL		INSUL		AMB							
H.P.		MTG		TYPE		R.P.M.		VOLTS		ENCL		PHASE		FREQ		FRAME	
REV. DESC: MOVED STARTER BOX TO CENTER OF MOTOR												BALDOR ELECTRIC Co. STD 14" BUFFER 37 FRAME W/ 'GE' MAGNETIC STARTER					
REV. LTR: A BY: JD REVISED: 01/07/00 2:15 TDR: 0199019																	
FILE: AAA00066298 MDL: -																	
MTL: -																	