



---

# Customer information packet

## 3AUA0000126719

DCS800-EP1-0045-05 E213 F278 M635

**Accessories**

| Part number | Description                             | Multiplier |
|-------------|-----------------------------------------|------------|
| 58948250    | FIBRE OPTIC CABLE NLWC-05 OPTION/SP KIT |            |
| 58948268    | FIBRE OPTIC CABLE NLWC-07 OPTION/SP KIT |            |
| 58948276    | NLWC-10 OPTION.SP KIT FIBRE OPTIC CABLE |            |
| 61046534    | TWIN FIBREOPT CA QFBR-3883(HFBR-END010  |            |
| 61059113    | TWIN FIBREOPT. CA 5,0 M                 | ES         |
| 61059121    | TWIN FIBREOPT. CA 2,0 M                 | ES         |
| 61059130    | TWIN FIBREOPT. CA 0,5 M                 |            |
| 64606778    | MODBUS ADAPTER RMBA-01 OPTION/SP KIT    |            |
| 64606816    | DIGITAL I/O EXTEN RDIO-01 OPTION/SP KIT |            |
| 64606841    | ANALOG I/O EXTENS RAIO-01 OPTION/SP KIT |            |
| 64606859    | RPBA-01 PROFIBUS-DP ADAPTER-KIT         | EG         |
| 64606905    | RCAN-01 CANOPEN OPTION/SP KIT           |            |
| 64610805    | PULSE ENCODER INT RTAC-01 OPTION/SP KIT | ES         |
| 64751701    | BAC, RCNA-01 Option                     | CT         |
| 64751727    | RETA-01 ETHERNET ADAPTOR MODULE KIT     | CT         |
| 68486408    | RESOLVER INTERFAC RRIA-01 OPTION/SP KIT |            |
| 68654947    | PULSE ENCODER INT RTAC-03 OPTION/SP KIT | ES         |
| 68805848    | PULSE ENCODER INTERFACE                 | ES         |