

BALDOR® • RELIANCE®

Customer information packet
3AUA0000152629

DCS800-EP1-0090-05 F278 M636

Accessories

Part number	Description	Multiplier
58948250	FIBRE OPTIC CABLE NLWC-05 OPTION/SP KIT	
58948268	FIBRE OPTIC CABLE NLWC-07 OPTION/SP KIT	
58948276	NLWC-10 OPTION.SP KIT FIBRE OPTIC CABLE	
61046534	TWIN FIBREOPT CA QFBR-3883(HFBR-END010	
61059113	TWIN FIBREOPT. CA 5,0 M	ES
61059121	TWIN FIBREOPT. CA 2,0 M	ES
61059130	TWIN FIBREOPT. CA 0,5 M	
64606778	MODBUS ADAPTER RMBA-01 OPTION/SP KIT	
64606816	DIGITAL I/O EXTEN RDIO-01 OPTION/SP KIT	
64606841	ANALOG I/O EXTENS RAIO-01 OPTION/SP KIT	
64606859	RPBA-01 PROFIBUS-DP ADAPTER-KIT	EG
64606905	RCAN-01 CANOPEN OPTION/SP KIT	
64610805	PULSE ENCODER INT RTAC-01 OPTION/SP KIT	ES
64751701	BAC, RCNA-01 Option	CT
64751727	RETA-01 ETHERNET ADAPTOR MODULE KIT	CT
68486408	RESOLVER INTERFAC RRIA-01 OPTION/SP KIT	
68654947	PULSE ENCODER INT RTAC-03 OPTION/SP KIT	ES
68805848	PULSE ENCODER INTERFACE	ES