


DUTY MASTER ALTERNATING CURRENT MOTORS

SQUIREL-CAGE INDUCTION
ENCLOSURE: TOTALLY ENCLOSED
SUBMERSIBLE

FRAME 210TY



DIMENSIONS ARE IN INCHES SEE SHEET 2 FOR MILLIMETERS

FRAME	C	L	P	T	UC(3)	V	W	AG	AH	AJ	AL(7)
210TY	36.41	21.12	11.50	2.25	1.250	2.00	.28	30.12	2.28	11.50	10.625
(1)											

FRAME	BUC2)	BE	BF	XR(4)	LEAD CONNECTION			B.E. KEYWAY			WEIGHT LBS.	
					X	Y	XD	BB	a	b		LENGTH
210TY	12.38	.75	.56	1/2-13	2-1/2-8	1.25	7.75	.12	.250	.12	11.2	315
(1)												

- (1) SPECIAL DIMENSIONS ON THIS LINE.

(2) "BD" VARIES ± .010

(3) "U" VARIES +.0000, -.0005

(4) TAP DEPTH ON 210TY IS 1.38
- (5) LEAD WIRE LENGTH AS SPECIFIED ON SALES ORDER

(6) MINIMUM SUBMERGED DEPTH.

(7) "AL" VARIES +.004, -.000.
- FACE ROUNDT AND ECCENTRICITY .008 MAX. T.I.R.
PROTECTIVE CONDUIT FURNISHED BY CUSTOMER.

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.

REV. DESC: LOAD TO BUS		
REV. LTR: -	VERSION: 00	TDR: 000000925374
FILE: \RGG\00025\103	REVISED: 10: 39: 07 05/14/2015	BY: RGGWT
MTL: -		

BALDOR

DIM SHT,210TY,SUBMERSIBLE

SH 1 of 1