

ENCLOSURE: DRIP-PROOF FULLY-GUARDED MOUNTING: FOOT, "C" FACE COOLING: SELF-VENTILATED ACCESSORIES: PROVISIONS FOR
SPLASHPROOF, TOTALLY ENCLOSED METHOD OF DRIVE: COUPLED OR BELTED NON-VENTILATED TACHOMETER MOUNTING
ONLY WHEN SPECIFIED

DC180ATY-DC180ATCZ



FRAME	FLANGE	C(S)	B	2F	DRIVE END SHAFT AND KEY										TERMINAL BOX DIMENSIONS										WT. LBS.
					N	N-W	UX	V	AH	R(3)	SQ	LGTH	AA	AB	AC	AD	AF	AX	Y	YZ					
DC189ATY	ND. 2	18.81	11.62	10.00	2.44	2.85	8750	2.00	2.12	771	188	1.38	1.00	7.30	6.11	2.19	4.38	3.75	3.25	130					
DC189ATCZ	ND. 1	19.44	11.62	10.00	3.06	2.68	1250	2.62	2.62	986	2.00	1.81	1.00	7.30	6.11	2.19	4.38	3.75	3.25	130					
DC1810ATY	ND. 2	19.56	12.38	11.00	2.44	2.85	8750	2.00	2.12	771	188	1.38	1.00	7.30	6.11	2.19	4.38	3.75	3.25	155					
DC1810ATCZ	ND. 1	20.19	12.38	11.00	3.06	2.68	1250	2.62	2.62	986	2.00	1.81	1.00	7.30	6.11	2.19	4.38	3.75	3.25	155					
DC1811ATY	ND. 2	21.06	13.88	12.50	2.44	2.85	8750	2.00	2.12	771	188	1.38	1.00	7.30	6.11	2.19	4.38	3.75	3.25	185					
DC1811ATCZ	ND. 1	21.69	13.88	12.50	3.06	2.68	1250	2.62	2.62	986	2.00	1.81	1.00	7.30	6.11	2.19	4.38	3.75	3.25	185					

- (1) "D" DIMENSION WILL NOT BE EXCEEDED. SHIMS UP TO .06 INCHES IN THICKNESS ARE USUALLY REQUIRED FOR COUPLED OR GEARED MACHINES. TOLERANCE +.00/-.06.
- (2) "U" VARIES +.0000, -.0005.
- (3) "R" VARIES +.000, -.015.
- (4) "AK" VARIES +.000, -.003.
FACE RUNOUT AND ECCENTRICITY .004 MAX. T. I. R.

- (5) WHEN THE MOTOR APPLICATION DOES NOT REQUIRE THE USE OF
OPP. DRIVE END, ADD .25 TO "C" DIM. FOR BRACKET COVER.
- (6) TERMINAL BOX CAN BE ROTATED TO REPOSITION CONDUIT
CONNECTION.
IF MOUNTING CLEARANCE DETAILS ARE REQUIRED
CONSULT FACTORY.
- (7) "BB" OF .25 IS A MINIMUM VALUE.

MOTOR WEIGHT MAY VARY 15% FOR NON-STANDARD RATINGS AND/OR ACCESSORIES.

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.

BALDOR - RELIANCE®

DIMENSION DRAWING,DC180ATY – DC180ATCZ,DPP,TENV,FOOT MTG.

SH 1 of 1