




D

C

B

A

D

C

B

A

35LYP565

35LYP565

(3524) = 17.29
(3536) = 18.36
(3548) = 19.36

4.72

2.06

1.88

.12

NAMEPLATE
BRACKET W/N.P.
& CAUTION LABEL

.0015 MAX,
CLEARANCE
(EA. END)

Ø 7.19

Ø 6.45

Ø .6250
Ø .6245
Ø 4.500
Ø 4.497

NOTE: BASE WELDED TO BAND

.31-18
THRUBOLTS

4 SLOTS
.34 WIDE

3.00

2.76

.66

4.32

BRUSH INSPECTION
PLUG 2 PLACES AT
180° - 5 THREAD
MIN. ENGAGEMENT

.09

.41

MAX GAP
.040

HEX BOLT

.006 (REF)
.016 MAX
CLEARNACE
(EA. END)

1.12

SECTION C-C

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: CONVERT AUTOCAD DRW TO SWD DRW			
REV: L	VERSION: 06	REVISED: 01:19:02 04/19/2023	TDR: 000001207032
MODEL NO. 35LYP565			REF: -
BY: ENALEM0			B

BALDOR - RELIANCE®

STD HORZ X35PM NEMA 56C XPFC, CL I GP D, CL II GP F&G