


ALUMINUM (MATT) BACKGROUND WITH BLACK LETTERS

LABEL MANUFACTURER  
IDENTIFYING MARK TO  
APPEAR HERE

FOR STRAIGHT SHUNT MOTORS: DISREGARD S1 AND S2.  
 FOR SERIES MOTORS: DISREGARD F1, F2, F3, F4.  
 STRAIGHT SHUNT: F1 AND A1 SAME POLARITY, ROTATION CCW.  
 SERIES: CONNECT A2 AND S1, ROTATION CCW.  
 STABILIZED SHUNT AND COMPOUND: F1 AND A1 SAME POLARITY. CONNECT  
 A2 AND S1, ROTATION CCW.  
 FOR CW ROTATION: INTERCHANGE A1 AND A2. ROTATION VIEWED FROM  
 OPPOSITE DRIVE END. FOR FIELD REVERSING MOTORS WITH A SERIES FIELD:  
 S1 MUST REVERSE POLARITY WHEN F1 REVERSES.  
 THERMOSTAT: WHEN SUPPLIED WILL HAVE LEADS TAGGED P1 AND P2.  
 THERMOSTAT SENSES HEAT OF COMMUTATING FIELD COIL.

AMPERE RATINGS OF CONTACTS.

| MAX AMPS BREAK |         |        | MAX CONTINUOUS     |
|----------------|---------|--------|--------------------|
| 120 VAC        | 240 VAC | 24 VDC | AMP - ALL VOLTAGES |
| 12             | 8       | 2      | 2                  |

SPACE HEATER: WHEN SUPPLIED WILL HAVE LEADS TAGGED H1 AND H2.  
 SEE MOTOR NAMEPLATE FOR HEATER VOLTAGE AND CURRENT.

15209

2 1/2

NOTE:

MATERIAL .005 MINIMUM FULL HARD  
 ALUMINUM DULL FINISH.  
 TEMP. RANGE -20°C TO +125°C  
 MAXIMUM.  
 FOR INDOOR AND OUTDOOR MOUNTING  
 BACK.  
 METAL, PRESSURE SENSITIVE BACK.  
 MUST MEET CSA STANDARD.  
 THE CSA IDENTIFYING MARK OF THE  
 LABEL MANUFACTURER MUST APPEAR  
 IN THE UPPER RIGHT HAND CORNER AS  
 INDICATED.

UNLESS OTHERWISE SPECIFIED,  
 BREAK ALL SHARP EDGES .010/.020.  
 REMOVE ALL BURRS.

## TOLERANCES

|            |                 |
|------------|-----------------|
| .X ±.015   | FRACTIONS ±1/32 |
| .XX ±.010  | RADI ±1/16      |
| .XXX ±.005 | ANGLES ±1°      |

MATL: NOTED

REV: G CHANGE ALL "NAMEPLATE" TEXT TO "LABEL"

60ZS1

|                   |              |                   |
|-------------------|--------------|-------------------|
| SCALE: -          | BY: BKW      | REVISED: 02/19/97 |
| FILE: CHB00002485 | TDR: 0115147 |                   |

BALDOR ELECTRIC Co.

LABEL, CONNECTIONS AND TERMINAL MARKINGS DC