

DUTY MASTER ALTERNATING CURRENT MOTORS





SQUIRREL-CAGE INDUCTION

ENCLOSURE: TOTALLY ENCLOSED

MOUNTING: FOOT, F-1

E364TS/E365TS FRAME MOUNTING HOLES

COOLING: FAN COOLED



DIMENSIONS ARE IN INCHES.
WEIGHT (LBS.) 800 / MOTOR WEIGHT MAY VARY 15% DEPENDING ON RATING.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

1 OBSTRUCTIONS MUST NOT ENCROACH ON AIR INLET.

IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
MAX PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .003" T.I.R.

REV. DESC: ADD METRIC DS	VERSION: 02	REVISED: 08:05:53 02/24/2023	TDR: 000001204722
MODEL NO. 617428-298	BY: USJEDIL		

BALDOR

E364/365TS TEFC F1 FOOT/CAST IRON CONDUIT BOX

DUTY MASTER ALTERNATING CURRENT MOTORS





SQUIRREL-CAGE INDUCTION

ENCLOSURE: TOTALLY ENCLOSED

MOUNTING: FOOT, F-1

E364TS/E365TS FRAME MOUNTING HOLES

COOLING: FAN COOLED



1 OBSTRUCTIONS MUST NOT ENCROACH ON AIR INLET.

IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
MAX PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .08 T.I.R.

DIMENSIONS ARE IN MILLIMETERS.
WEIGHT (KG) 363, MOTOR WEIGHT MAY VARY +/-15% DEPENDING ON RATING.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

REV. DESC: ADD METRIC DS	VERSION: 02	REVISED: 08:05:53 02/24/2023	TDR: 000001204722
MODEL NO. 617428-298			
BY: USJEDIL			

BALDOR

E364/365TS TEFC F1 FOOT/CAST IRON CONDUIT BOX