

35LYNN878

$$\begin{array}{r} 510-520 = 11.13 \\ 521-524 = 11.63 \\ -525-528 = 12.13 \\ 529-535 = 13.00 \\ 536-546 = 14.38 \end{array}$$

GREASE FITTING
(EA. END)


 .19 KEY
 1.38 LONG

$$- \phi \begin{matrix} .8750 \\ .8745 \end{matrix}$$

6 HOLES
Ø.38

— LEAD HOLE
Ø1.09

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: UPDATE 3D MODEL BOM PER REV C, NO CHG TO 2D PRINT			
REV: C	VERSION: 03	REVISED: 09:44:37 04/01/2022	TDR: 000001188385
MODEL NO. 35LYNN878			REF: -
BY: USBUFRA			B

BALDOR - RELIANCE®

STD HOR 143-5T OPSB 35M F2 W/1.09 LEAD HOLE
SH 1 OF 1

35LYNN878