

ABB BALDOR RELIANCE III

Customer information packet

EJMM4106T-G

20HP, 3520RPM, 3PH, 60HZ, 256JM, 0936M, TEFC, F

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	256JM
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	20.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CURUSEEV NEMA PREMIUM
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	50.000 A @ 208.0 V 46.000 A @ 230.0 V 23.000 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	23.0 a
Insulation Class	H

Part Detail

Revision	G
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	09WGZ601
Layout	09LY-001-158
Eff. date	06-29-2026
CD Diagram	CD0005
Poles	02
Leads	9#10
Proprietary	False
Created date	02-22-2021

Inverter Code	Inverter Ready
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0936M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	25.36 IN
Power Factor	89
Product Family	General Purpose
Pulley Face Code	C-Face
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.250 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Speed	3520 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3441LUA									
CAT.NO.	EJMM4106T-G								
SPEC	09-0000-2897								
HP	20								
VOLTS	230/460								
AMPS	46/23								
RPM	3520								
FRAME	256JM		HZ	60			PH	3	
SF	1.15		CODE	H	DES	A	CLASS	H	
NEMA NOM. EFF	91		PF	89					
RATING	40C AMB-CONT								
CC	010A								
ENCL	TEFC	SER							
DE	6309		ODE	6208					
VPWM INVERTER READY									
CT6-60H(10:1)VT3-60H(20:1									
50HZ 20HP 190/380V 56/28A									SF1.0



