

DUTY MASTER ALTERNATING CURRENT MOTORS
SQUIRREL-CAGE INDUCTION

617428-431





ENCLOSURE: OPEN DRIP-PROOF

MOUNTING: FOOT, F-1 SIDE

E405TS/E404TS FRAME MOUNTING HOLES

COOLING: SELF-VENTILATED

MAIN STEEL CONDUIT BOX



DIMENSIONS ARE IN INCHES.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

REV. DESC: UPDATE MODEL TO ADD EXTERNAL HARDWARE PER PROD MGM			
REV: B	VERSION: 02	REVISED: 12:57:54 07/15/2022	TDR: 000001193529
MODEL NO. 617428-431			
BY: USBUFRA			

BALDOR

E405/404TS ODP FOOT F1 STEEL CONDUIT BOX

MAX PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .003" T.I.R.

617428-431