

DUTY MASTER ALTERNATING CURRENT MOTORS

SQUIRREL-CAGE INDUCTION





ENCLOSURE: OPEN DRIP-PROOF

MOUNTING: FOOT, F-1

E449TS FRAME MOUNTING

COOLING: NON-VENTILATED

14X14X12 STEEL C/BOX



DIMENSIONS ARE IN INCHES.
WEIGHT (LBS) 2100. MAY VARY 15% DEPENDING ON RATING.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

SHEET NUMBER
1 OF 1

IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.

S66-686P09

MAX PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .003 T.I.R.

| | | | |
|---|-------------|------------------------------|-------------------|
| REV. DESC: UPDATE MODEL TO ADD EXTERNAL HARDWARE PER PROD MGM | | | |
| REV: A | VERSION: 01 | REVISED: 06:55:35 07/14/2022 | TDR: 000001193529 |
| MODEL NO. 604989-595 | | | |
| BY: USBUFRA | | | |

BALDOR

E449TS TEAO/ODP F1 FOOT/FABRICATED 14X14X12 STEEL BOX