

ABB BALDOR RELIANCE III

Customer information packet EM2540T-G

40HP, 1180RPM, 3PH, 60HZ, 364T, 4278M, OPSB, F1

Specifications

Enclosure	OPSB
Frame	364T
Frame Material	Steel
Frequency	60.00 Hz
Motor Letter Type	Three Phase
Output @ Frequency	40.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA CSA EEV UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	110.000 A @ 208.0 V 51.000 A @ 460.0 V 104.000 A @ 230.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	94.1 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	51.0 a

Part Detail

Revision	T
Type	AC
Mech. spec.	42E260
Base	
Status	PRD/A
Elec. spec.	42WGW920
Layout	42LYE260
Eff. date	11-29-2023
CD Diagram	CD0005
Poles	06
Leads	9#8
Proprietary	False
Created date	11-30-2011

Insulation Class	H
Inverter Code	Inverter Ready
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 8 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	4278M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	30.69 IN
Power Factor	79
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	2.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1180 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP2138LUA												
CAT.NO.	EM2540T-G			P/N					ENCLOSURE			OPSB
SPEC.	42E260W920G1		CC	010A	FRAME		364T		S/N			
HP	40			CLASS		H	HZ		60			
RPM	1180			PH	3	DES		A				
VOLT	230/460			KVA-CODE			H		ODE BRG	6311	DE BRG	6313
AMP	104/51											
RATING	40C AMB-CONT			GREASE			POLYREX EM					
NEMA-NOM-EFF	94.1	PF	79	SER.F.	1.15							
	50HZ 40HP 190/380V 120/60A						SF1.0					
HTR-VOLTS	HTR-AMPS											

AC Induction Motor Performance Data

Record # 36099

Typical performance - not guaranteed values

Winding: 42WGW920-R002				Type: 4278M		Enclosure: OPSB	
Nameplate Data				460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		40		Full Load Torque		178 LB-FT	
Volts		230/460		Start Configuration		direct on line	
Full Load Amps		104/51		Breakdown Torque		521 LB-FT	
R.P.M.		1180		Pull-up Torque		232 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque		317 LB-FT	
NEMA Design Code		A	KVA Code	Starting Current		337 A	
Service Factor (S.F.)		1.15		No-load Current		21.9 A	
NEMA Nom. Eff.		94.1	Power Factor	Line-line Res. @ 25°C		0.154 Ω	
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		41°C	
S.F. Amps				Temp. Rise @ S.F. Load		50°C	
				Locked-rotor Power Factor		28	
				Rotor inertia		14.9 LB-FT2	

Load Characteristics 460 V, 60 Hz, 40 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	43	64	74	79	81	82	80
Efficiency	89.3	93.1	94.1	94.1	93.3	92.2	93.6
Speed	1195	1191	1187	1183	1177	1170	1179
Line amperes	24.8	31.6	40.5	50.9	62.2	77.5	57.7

ABB Motors and Mechanical Inc.

WINDING # 42WGW920

Typical performance - not guaranteed values.

40 HP 3 PH 60 HZ 1180 RPM 460 V 4278M

TORQUES (LB-FT): PO=521 PU=232 LR=317 LRA=337





