

D

C

B

A

- 5.16

- 5.57 -

- 5.25

$$-\phi \begin{array}{c} 2.125 \\ 2.124 \end{array}$$

_GREASER & PLUG
(EA. END)

8 HOLES
Ø.66

- 10.50 —

_____ 10.50

— 12.00 —

— 13.75 —

88

- 5.25

SHAFT GROUND
(BP5338A04)

6312

DRIVE END DETAIL

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: LOAD TO SW & UPDATE NP GRAPHICS TO MATCH NP ON CAT			
REV: C	VERSION: 03	REVISED: 12:34:16 11/02/2022	TDR: 000001194199
MODEL NO. 42LYE307			REF: -
BY: USBUFA			B

BALDOR®

HOR OPSB 324-6T W/INT SH GND

42LYE307

D

C

B

A