





- NOTES:
- SHAFT STANDARDS PER 3425
 - ▽ X/P SURFACE PER DWG. 402111-A

TOLERANCE UNLESS OTHERWISE SHOWN:	
ONE PLACE DECIMAL	±0.1
TWO PLACE DECIMAL	±0.02
THREE PLACE DECIMAL	±0.003
ANGLE	±0°-30'
SURFACE FINISH	250



1	CORE KEY	34180-160	GA		
1	FINISHED SHAFT	4.25 X 46.73		FSCL1	153.3
RA	NAME	SIZE OR CASTING	SYM	46024-	WT. (LB.)

BALDOR-DODGE-RELIANCE PROPRIETARY & CONFIDENTIAL:
THIS DRAWING IS THE PROPERTY OF BALDOR-DODGE-RELIANCE
AND/OR ITS SUBSIDIARIES AND IS NOT TO BE USED, DUPLICATED
OR DISCLOSED WITHOUT THE EXPRESS WRITTEN PERMISSION
OF THE COMPANY.

REV. DESC: CHG B-B DIM FROM 32.09 TO 32.051			
REV: B	VERSION: 02	REVISED: 10:41:55 03/25/2015	TDR: 000000895904
MODEL NO. 611787-137		REF:	
BY: RAGHZT	Material:	B	

BALDOR

SHAFT E449T PROT 6318-6318 BRGS W/ PLUG AT ODE

611787-137