DUTY MASTER ALTERNATING CURRENT MOTORS

SQUIRREL-CAGE INDUCTION

ENCLOSURE: TOTALLY ENCLOSED


FRAME 449TS ABOVE NEMA RATINGS (3600 RPM MAX)

COOLING: FAN COOLED

2

MOUNTING: FOOT

INCLUDES 447TS FRAME MOUNTING HOLES



5

4

3

DUTY MASTER ALTERNATING CURRENT MOTORS

SQUIRREL-CAGE INDUCTION

ENCLOSURE: TOTALLY ENCLOSED


FRAME 449TS ABOVE NEMA RATINGS (3600 RPM MAX)

COOLING: FAN COOLED

2

MOUNTING: FOOT

INCLUDES 447TS FRAME MOUNTING HOLES



5

GROUND HOLES QTY 1 1/2-13 TAP; QTY 1 3/8-16 TAP

VARIES +.0,-1.5 VARIES +.00,-.03

MOTOR WEIGHTS MAY VARY BY 15% DEPENDING ON RATING. OBSTRUCTION MUST NO ENCROACH ON AIR INLET

CONDUIT BOX LOCATED ON OPPOSITE SIDE WHEN F-2. IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY. MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .08 MM T.I.R. TO 127 MM DIA.

5 WEIGHT (KGS): 1400

DRIVE END AIR DEFLECTOR IS ONLY INCLUDED WHEN NECESSARY.

DIMENSIONS ARE IN MILLIMETERS

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

REV. DESC: NEW DRAWING				PAT DOP	
REV: -	VERSION: 00	REVISED: 11:13:38 04/02/2015	TDR: 000000918312		
MODEL NO. 617427-445				G449TS/447TS-FOOTED-SIDE/CENTER CONDUIT BOX-14X14X12	
BY: RAGEC				U44915/44/15-FUU1ED-SIDE/CENTER CONDUIT BUA-14A14A12	

SHEET NUMBER 2 OF 2 Stt-724719