

**BALDOR • RELIANCE**

---

**Customer information packet**  
**ERH110E4H7CE4**

7.5HP, 1800RPM, 3PH, 50/60HZ, 178, TEAO, 460V

**Part detail**

<b>Revision</b>	G
<b>Type</b>	AC
<b>Mech. spec.</b>	
<b>Base</b>	
<b>Status</b>	SMP/A
<b>Elec. spec.</b>	
<b>Layout</b>	
<b>Eff. date</b>	01-09-2025
<b>CD Diagram</b>	
<b>Poles</b>	///
<b>Leads</b>	
<b>Proprietary</b>	False
<b>Created date</b>	03-18-2024

**Nameplate**

NP4557D02						
<b>CAT #</b>	ERH110E4H7CE4			<b>CLASS</b>	F	
<b>SPEC</b>	ERH110E4H7CE4-001			<b>YEAR OF MANUFACTURE</b>		
<b>CUST P/N</b>				<b>IP</b>	65	
<b>SER #</b>			<b>WT</b>	20.820	<b>KG</b>	
<b>HP/KW</b>	7.5/5.6	<b>VOLTS</b>	460	<b>AMPS</b>	8.7	
<b>R.P.M. (1/MIN)</b>	1800	<b>HZ</b>	50/60			
<b>EFF</b>			<b>ENCL</b>	TEAO	<b>IC</b>	418