

ABB BALDOR RELIANCE III

Customer information packet

HBEM3615T

42M 4P TEFC HOR 184T

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	184T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	5.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	CURUSEEV NEMA PREMIUM WEEE
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	14.000 A @ 208.0 V 6.700 A @ 460.0 V 13.400 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Electrically Isolated Bearings
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater

Part Detail

Revision	G
Type	AC
Mech. spec.	36T429
Base	
Status	PRD/A
Elec. spec.	36WGQ032
Layout	36LYT429
Eff. date	03-27-2026
CD Diagram	CD0005
Poles	04
Leads	9#16
Proprietary	False
Created date	01-05-2022

High Voltage Full Load Amps	6.7 a
Insulation Class	H
Inverter Code	Inverter Ready
KVA Code	J
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Max Speed	2700 rpm
Motor Lead Quantity/Wire Size	9 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3642M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	18.04 IN
Power Factor	78
Product Family	General Purpose
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1755 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

AC Induction Motor Performance Data

Record # 85675

Preliminary Data Sheet

Winding: 36WGQ032-RXXX			Type: 3642M		Enclosure: TEFC	
Nameplate Data			460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		5	Full Load Torque		15 LB-FT	
Volts		230/460	Start Configuration		direct on line	
Full Load Amps		13.4/6.7	Breakdown Torque		53.1 LB-FT	
R.P.M.		1755	Pull-up Torque		23.4 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque		34.7 LB-FT
NEMA Design Code		B	KVA Code	Starting Current		49.8 A
Service Factor (S.F.)		1.15	No-load Current		3.31 A	
NEMA Nom. Eff.		89.5	Power Factor	Line-line Res. @ 25°C		2.38 Ω
Rating - Duty		40C	AMB-CONT	Temp. Rise @ Rated Load		71°C
S.F. Amps		15/7.5	Temp. Rise @ S.F. Load		92°C	
			Locked-rotor Power Factor		49	
			Rotor inertia		0.391 lb-ft²	

Load Characteristics 460 V, 60 Hz, 5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	39	60	72	79	82	84	81
Efficiency	84.4	89.4	90.1	89.6	88.4	86.8	88.5
Speed	1789	1778	1766	1753	1738	1722	1741
Line amperes	3.64	4.39	5.45	6.66	8.08	9.67	7.52

ABB Motors and Mechanical Inc.

WINDING # 36WGQ032

Typical performance - not guaranteed values.

5 HP 3 PH 60 HZ 1755 RPM 460 V 3642M

TORQUES (LB-FT): PO=53.1 PU=23.4 LR=34.7 LRA=49.8





