

BALDOR® • RELIANCE™

Customer information packet

HDS100-0619ARKNN

HDS100-0619ARKNN, RES, KEY, 230V

Specifications


Bearing Grease Type	Polyrex EM
Dimensional Drawing Numbers	HD100LYA001
Nameplate Amps	10.0

Part detail

Revision	D
Type	
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	
Layout	HD100LYA001
Eff. date	04-09-2018
CD Diagram	
Poles	
Leads	
Proprietary	False
Created date	08-10-2017

Nameplate

LB1577T01									
MODEL:	HDS100-0619ARKNN								
PN	1.9	KW	TO	6.0	N.M	IO	10.0	A	
U	230	V	TP	18.0	N.M	IP	32.0	A	
NN/N MAX	3000/4000		RPM	3XPTC130					
FBK	RES	IP	IP54		INS F				
BRK:	VDC/		N.M						
S/N									



MOTOR TYPE	L [mm]	MOMENT OF INERTIA [kg.cm ²]		WEIGHT [kg]	
		WITH BRAKE	WITHOUT BRAKE	230V	
				WITH BRAKE	WITHOUT BRAKE
HDS100-0206xRKxx	189.5	0.951	0.821	4.47	3.70
HDS100-0206xE(S/M/S2/M2)Kxx		0.885	0.755		
HDS100-0206xD3(4)Kxx		0.824	0.694		
HDS100-0413xRKxx	213.5	1.496	1.366	5.47	4.70
HDS100-0413xE(S/M/S2/M2)Kxx		1.431	1.301		
HDS100-0308xE(S/M/S2/M2)Kxx		1.369	1.239		
HDS100-0619xRKxx	237.5	2.040	1.910	6.27	5.50
HDS100-0619xE(S/M/S2/M2)Kxx		1.975	1.845		
HDS100-0619xD3(4)Kxx		1.913	1.783		
HDS100C-0206xRKxx	189.5	2.186	2.056	4.8	4.0
HDS100C-0206xE(S/M/S2/M2)Kxx		2.128	1.998		
HDS100C-0206xD3(4)Kxx		2.068	1.938		
HDS100C-0413xRKxx	213.5	2.867	2.737	5.8	5.0
HDS100C-0308xE(S/M/S2/M2)Kxx		2.809	2.679		
HDS100C-0413xD3(4)Kxx		2.749	2.619		
HDS100C-0619xRKxx	237.5	3.538	3.408	6.6	5.8
HDS100C-0619xE(S/M/S2/M2)Kxx		3.480	3.350		
HDS100C-0619xD3(4)Kxx		3.420	3.290		


NOTES:
 1. DIMENSIONS: mm
 2. NOT TOLERANCE DIMENSIONS ±1mm


REV. DESC: REVISE CODE FOR HIPERFACE ENCODER MOTOR			
REV: D	VERSION: 04	REVISED: 03:39:54 04/22/2019	TDR: 000001106375
MODEL NO. HD100LYA001		REF: -	
BY: CNLYLIN4	Material: -		

BALDOR

HDS100 LAYOUT, RES, ENC, KEY, OPTIONAL BRAKE, SEAL

CD2167A09

MOTOR & BRAKE & PTC LEADS			
 <p>WD1456A26 (PLUG SIDE)</p>	PIN	FUNCTION	COLOR
	1	U (R)	BLACK
	2	GROUND (PE)	YELLOW/GREEN
	3	W (T)	BLUE
	4	V (S)	RED
	A	PTC	BLUE BLACK
	B	PTC	BLUE
	C	BRAKE	RED
	D	BRAKE	BLUE

RESOLVER LEADS			
 <p>WD1456A21 (PLUG SIDE)</p>	PIN	FUNCTION	COLOR
	1	R1 (REF+)	RED/WHITE
	2	R2 (REF-)	YELLOW/WHITE
	3	S1 (COS+)	RED
	4	S3 (COS-)	BLACK
	5	S4 (SIN-)	BLUE
	6	S2 (SIN+)	YELLOW
	7~17	-	-

REV. DESC: ENGINEERING CHANGE			
REV: B	VERSION: 02	REVISED: 04:41:51 03/04/2024	TDR: 000001227267
60A71DC	MODEL NO. CD2167A09		REF: -
	BY: CNCONIE	Material: -	

BALDOR

CONNECTION DIAGRAM, POWER & RESOLVER

CD2167A09