

BALDOR® • RELIANCE™

Customer information packet

HDS180-2540BRKNN

HDS180-2540BRKNN, RES, KEY

Specifications

Bearing Grease Type	Polyrex EM
Dimensional Drawing Numbers	HD180LYA001
Nameplate Amps	16.5

Part detail

Revision	C
Type	
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	
Layout	HD180LYA001
Eff. date	02-03-2021
CD Diagram	
Poles	
Leads	
Proprietary	False
Created date	02-27-2018

Nameplate

LB1577T01

MODEL:	HDS180-2540BRKNN								
PN	4.0	KW	TO	25.0	N.M	IO	16.5	A	
U	400	V	TP	75.0	N.M	IP	50.5	A	
NN/N MAX	1500/3500		RPM	3XPTC130					
FBK	RES		IP	IP54	INS F				
BRK:		VDC/		N.M					
S/N									



