

**BALDOR® • RELIANCE®**

---

# Customer information packet

## HDS180-3555BEKNN

HDS180-3555BEKNN, INC.ENC, KEY

**Specifications**

<b>Bearing Grease Type</b>	Polyrex EM
<b>Dimensional Drawing Numbers</b>	HD180LYA001
<b>Nameplate Amps</b>	21.5

**Part detail**

<b>Revision</b>	B
<b>Type</b>	
<b>Mech. spec.</b>	
<b>Base</b>	
<b>Status</b>	PRD/A
<b>Elec. spec.</b>	
<b>Layout</b>	HD180LYA001
<b>Eff. date</b>	05-13-2019
<b>CD Diagram</b>	
<b>Poles</b>	
<b>Leads</b>	
<b>Proprietary</b>	False
<b>Created date</b>	02-27-2018

**Nameplate****LB1577T01**

<b>MODEL:</b>	HDS180-3555BEKNN								
<b>PN</b>	5.5	<b>KW</b>	<b>TO</b>	35.0	<b>N.M</b>	<b>IO</b>	21.5	<b>A</b>	
<b>U</b>	400	<b>V</b>	<b>TP</b>	105.0	<b>N.M</b>	<b>IP</b>	70.4	<b>A</b>	
<b>NN/N MAX</b>	1500/3500		<b>RPM</b>	3XPTC130					
<b>FBK</b>	ENC		<b>IP</b>	IP54		<b>INS F</b>			
<b>BRK:</b>	VDC/		N.M						
<b>S/N</b>									



