

BALDOR® • RELIANCE™

Customer information packet

HDS180-3555BEKNN

HDS180-3555BEKNN, INC.ENC, KEY

Specifications

Bearing Grease Type	Polyrex EM
Dimensional Drawing Numbers	HD180LYA001
Nameplate Amps	21.5

Part detail

Revision	B
Type	
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	
Layout	HD180LYA001
Eff. date	05-13-2019
CD Diagram	
Poles	
Leads	
Proprietary	False
Created date	02-27-2018

Nameplate**LB1577T01**

MODEL:	HDS180-3555BEKNN								
PN	5.5	KW	TO	35.0	N.M	IO	21.5	A	
U	400	V	TP	105.0	N.M	IP	70.4	A	
NN/N MAX	1500/3500		RPM	3XPTC130					
FBK	ENC		IP	IP54		INS F			
BRK:	VDC/		N.M						
S/N									



