

ABB BALDOR RELIANCE III

Customer information packet HDS180-3555BGKNN

HDS180-3555BGKNN, DSL ENC(SINGAL-TURN), K

Specifications

| | |
|------------------------------------|-------------|
| Bearing Grease Type | Polyrex EM |
| Dimensional Drawing Numbers | HD180LYA002 |
| Nameplate Amps | 21.5 |

Part Detail

| | |
|---------------------|-------------|
| Revision | C |
| Type | |
| Mech. spec. | |
| Base | |
| Status | PRD/A |
| Elec. spec. | |
| Layout | HD180LYA002 |
| Eff. date | 05-13-2019 |
| CD Diagram | |
| Poles | |
| Leads | |
| Proprietary | False |
| Created date | 02-27-2018 |

Nameplate

LB1577T01

| | | | | | | | | | |
|-----------------|------------------|-----------|------------|----------|------------|--------------|------|----------|--|
| MODEL: | HDS180-3555BGKNN | | | | | | | | |
| PN | 5.5 | KW | TO | 35.0 | N.M | IO | 21.5 | A | |
| U | 400 | V | TP | 105.0 | N.M | IP | 70.4 | A | |
| NN/N MAX | 1500/3500 | | RPM | 3XPTC130 | | | | | |
| FBK | S.DSL | | IP | IP54 | | INS F | | | |
| BRK: | VDC/ | | N.M | | | | | | |
| S/N | | | | | | | | | |



