

ABB BALDOR RELIANCE III

Customer information packet

HDS180-4876BEKNN

HDS180-4876BEKNN, INC.ENC, KEY

Specifications

Bearing Grease Type	Polyrex EM
Dimensional Drawing Numbers	HD180LYA001
Nameplate Amps	30.5

Part Detail

Revision	B
Type	
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	
Layout	HD180LYA001
Eff. date	05-13-2019
CD Diagram	
Poles	
Leads	
Proprietary	False
Created date	02-27-2018

Nameplate

LB1577T01

MODEL:	HDS180-4876BEKNN								
PN	7.6	KW	TO	48.0	N.M	IO	30.5	A	
U	400	V	TP	144.0	N.M	IP	101.0	A	
NN/N MAX	1500/3500		RPM		3XPTC130				
FBK	ENC		IP	IP54	INS F				
BRK:	VDC/			N.M					
S/N									



