

ABB BALDOR RELIANCE III

Customer information packet HDS180-4876BGKNN

HDS180-4876BGKNN, DSL ENC(SINGAL-TURN), K

Specifications

Bearing Grease Type	Polyrex EM
Dimensional Drawing Numbers	HD180LYA002
Nameplate Amps	30.5

Part Detail

Revision	C
Type	
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	
Layout	HD180LYA002
Eff. date	05-13-2019
CD Diagram	
Poles	
Leads	
Proprietary	False
Created date	02-27-2018

Nameplate**LB1577T01**

MODEL:	HDS180-4876BGKNN								
PN	7.6	KW	TO	48.0	N.M	IO	30.5	A	
U	400	V	TP	144.0	N.M	IP	101.0	A	
NN/N MAX	1500/3500		RPM	3XPTC130					
FBK	S.DSL		IP	IP54		INS F			
BRK:	VDC/		N.M						
S/N									



