



Customer information packet

HDS65-0102ASKNN

HDS65-0102ASKNN, ABS ENCODER, KEY

Specifications

Bearing Grease Type	Polyrex EM
Dimensional Drawing Numbers	HD65LYA005
Nameplate Amps	1.7

Part detail

Revision	E
Type	
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	
Layout	HD65LYA005
Eff. date	04-09-2018
CD Diagram	
Poles	
Leads	
Proprietary	False
Created date	08-16-2017

Nameplate

LB1577T01									
MODEL:	HDS65-0102ASKNN								
PN	0.2	KW	TO	0.6	N.M	IO	1.7	A	
U	230	V	TP	1.8	N.M	IP	6.0	A	
NN/N MAX	3000/5000			RPM	3XPTC130				
FBK	A.ABS		IP	IP54		INS F			
BRK:	VDC/				N.M				
S/N									



