

ABB BALDOR RELIANCE III

Customer information packet

HDS65-0104ASKNN

HDS65-0104ASKNN, ABS ENCODER, KEY

Specifications

Bearing Grease Type	Polyrex EM
Dimensional Drawing Numbers	HD65LYA005
Nameplate Amps	3.2

Part Detail

Revision	E
Type	
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	
Layout	HD65LYA005
Eff. date	04-09-2018
CD Diagram	
Poles	
Leads	
Proprietary	False
Created date	08-16-2017

Nameplate

LB1577T01									
MODEL:	HDS65-0104ASKNN								
PN	0.4	KW	TO	1.2	N.M	IO	3.2	A	
U	230	V	TP	3.6	N.M	IP	11.0	A	
NN/N MAX	3000/5000			RPM	3XPTC130				
FBK	S.ABS			IP	IP54	INS F			
BRK:	VDC/				N.M				
S/N									



