




RPM-AC FINNED FRAME VARIABLE SPEED ALTERNATING CURRENT MOTOR
FL5824-TEBC

ENCLOSURE: TOTALLY ENCLOSED
MOUNTING: F3, FOOT MOUNT

COOLING: BLOWER COOLED

619708-013



- NOTES:
1. MOTOR WEIGHTS MAY VARY +/- 15%
 2. SHAFT RUNOUT 0.003 T.I.R. MAX
 3. DIMENSIONS ARE IN INCHES
 4. FOR COUPLED DUTY ONLY
 5. AUX. C/BOXES ONLY WHEN BEARING RTD'S ARE SPECIFIED

FL5824	7240
FRAME SIZE	WT (LBS)

REV. DESC: INITIAL RELEASE			
REV: -	VERSION: 00	REVISED: 03:02:47 07/27/2021	TDR: 000001172668
MODEL NO. 619708-013			
BY: USWATUR		B	

BALDOR

DIM SHEET,FL5824-TEBC,FOOT MNT MOTOR,F3, 24X24X18 BOX

BALDOR DODGE RELIANCE PROPRIETARY & CONFIDENTIAL: THIS DRAWING IS THE PROPERTY OF BALDOR DODGE RELIANCE. IT IS TO BE USED FOR THE PROJECT AND NOT BE REPRODUCED OR DISCLOSED WITHOUT THE EXPRESS WRITTEN PERMISSION OF THE COMPANY.

619708-013