

DUTY MASTER ALTERNATING CURRENT MOTORS

SQUIRREL-CAGE INDUCTION




ENCLOSURE: TOTALLY ENCLOSED

FRAME 365T

COOLING: FAN-COOLED

MOUNTING: FOOT

INCLUDES 364T FRAME MOUNTING HOLES



DIMENSIONS ARE IN INCHES

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

REV. DESC: UPDATE D/S TO SHOW 3"NPT CALLOUT FOR C/B			
REV: A	VERSION: 01	REVISED: 08:14:59 11/18/2015	TDR: 000000953968
MODEL NO. 616512-504			
BY: RAGJSS1			

BALDOR

E365T 6313 FCXP W/BOLT ON COND BOX CL 1 GR C,D CL 2 GR F,G

SHEET NUMBER
1 OF 1

616512-504

IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF
STANDARD SHAFT EXTENSION IS .001" T.I.R.

616512-504