

BALDOR • RELIANCE

Customer information packet

37B101T920H1

3HP, 1160RPM, 3PH, 60HZ, 213T, 3723M, OPSB, F1

Part detail

Revision	N
Type	AC
Mech. spec.	37B101
Base	
Status	NLA/A
Elec. spec.	37WGT920
Layout	37LYB101
Eff. date	09-22-2015
CD Diagram	CD0005
Poles	06
Leads	9#14
Proprietary	True
Created date	01-01-0001

Nameplate

NP1256L									
CAT.NO.	11088								
SPEC.	37B101T920H1								
HP	3								
VOLTS	208-230/460								
AMP	9.9-9.2/4.6								
RPM	1160								
FRAME	213T		HZ	60		PH	3		
SER.F.	1.15	CODE	J	DES	B	CLASS	B		
NEMA-NOM-EFF	86.5	PF	70						
RATING	40C AMB-CONT								
CC									
DE	6307		ODE	6206					
ENCL	OPSB	SN							
	NOT FOR USE IN USA								

Accessories

Part number	Description	Multiplier
37-1404	C FACE KIT	A8