

DUTY MASTER ALTERNATING CURRENT MOTORS

617429-715

SQUIRREL-CAGE INDUCTION

COOLING: FAN COOLED





ENCLOSURE: TOTALLY ENCLOSED

MOUNTING: FOOT; F-1

FRAME G405T
INCLUDES G404T FRAME MOUNTING HOLES

ENCLOSURE ENHANCEMENT: SEVERE DUTY

CAST IRON BOX



DIMENSIONS ARE IN INCHES
IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .003" T.I.R.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

REV. DESC: NEW DRAWING			
REV: -	VERSION: 00	REVISED: 01:55:43 03/18/2016	TDR: 000000971431
MODEL NO. 617429-715		REF:	
BY: USJEDIL		Material:	

BALDOR

G405T/404T F1 FOOTED TEFC S/C CI C/BOX V-RING SLINGERS

SHEET NUMBER
1 OF 1

617429-715

1 OBSTRUCTION MUST NOT ENCROACH ON AIR INLET

617429-715