

DUTY MASTER ALTERNATING CURRENT MOTORS


SQUIREL-CAGE INDUCTION

611740-001-SH2

ENCLOSURE: TOTALLY ENCLOSED
MOUNTING: FOOT

FRAMES 250T THRU 440T

COOLING: FAN COOLED



DIMENSIONS ARE IN MILLIMETERS. SEE SHEET 1 FOR DIMENSIONS IN INCHES

FRAME	A	D(2)	E	G	H	J	K	O	P	T	AA(7)	AB	AC	AF	BA	EV
254T-256T	317.5	158.8	127.0	19.0	14.2	63.5	--	336.5	336.5	62.0	1-1/4	273.0	222.3	63.5	108.0	25.4
284T-286TS	349.2	177.8	139.7	19.0	14.2	63.5	--	374.6	378.0	62.0	1-1/2	333.8	254.0	81.0	120.7	25.4
324T-326TS	393.7	203.2	158.8	22.4	17.5	69.9	114.3	423.9	431.8	62.0	2	365.8	290.6	108.0	133.3	35.1
364T-365TS	431.8	228.6	177.8	22.4	17.5	69.9	98.6	469.9	495.3	74.7	3	458.7	355.6	136.7	149.4	35.1
404T-405TS	482.6	254.0	203.2	28.4	20.6	82.5	117.3	541.3	571.5	74.7	3	490.5	387.3	136.7	168.1	28.7
444T-445TS	533.4	279.4	228.6	28.4	20.6	82.5	133.3	593.9	641.3	82.5	3	593.9	460.2	165.1	190.5	31.7

(1)

FRAME	C	BS	B	2F	(4)	N	N-(W6)	U(3)	V	SO	LGTH.	WEIGHT
SIZE												KGS. (5)
254T	623.8	127.0	304.8	---	209.6	104.6	101.6	41.27	95.3	9.52	73.2	138
256T	623.8	127.0	304.8	254.0	---	104.6	101.6	41.27	95.3	9.52	73.2	142
284T	697.0	139.7	330.2	---	241.3	127.0	117.3	47.63	111.3	12.70	82.5	197
284TS	661.9	139.7	330.2	---	241.3	91.9	82.5	41.27	76.2	9.52	47.8	197
286T	697.0	139.7	330.2	278.4	---	127.0	117.3	47.63	111.3	12.70	82.5	204
286TS	661.9	139.7	330.2	278.4	---	91.9	82.5	41.27	76.2	9.52	47.8	204
324T	773.2	152.4	374.6	---	266.7	142.7	133.3	53.97	127.0	12.70	90.8	244
324TS	735.1	152.4	374.6	---	266.7	104.6	95.3	47.63	127.0	12.70	50.8	244
326T	773.2	152.4	374.6	304.8	---	142.7	133.3	53.97	127.0	12.70	90.8	263
326TS	735.1	152.4	374.6	304.8	---	104.6	95.3	47.63	127.0	12.70	50.8	263
364T	849.4	155.4	381.0	---	285.7	158.8	149.4	60.33	142.7	15.88	108.0	362
364TS	795.3	155.4	381.0	---	285.7	104.6	95.3	47.63	142.7	15.88	108.0	360
365T	849.4	155.4	381.0	311.1	---	158.8	149.4	60.33	142.7	15.88	108.0	381
365TS	795.3	155.4	381.0	311.1	---	104.6	95.3	47.63	142.7	15.88	108.0	378
404T	973.1	174.8	406.4	---	311.1	190.5	184.1	73.02	177.8	19.05	142.7	508
404TS	896.9	174.8	406.4	---	311.1	114.3	108.0	53.97	101.6	12.70	69.9	503
405T	973.1	174.8	406.4	349.2	---	190.5	184.1	73.02	177.8	19.05	142.7	526
405TS	896.9	174.8	406.4	349.2	---	114.3	108.0	53.97	101.6	12.70	69.9	522
444T	1133.3	209.6	482.6	---	368.3	227.1	215.9	85.72	209.6	22.22	174.8	698
444TS	1038.4	209.6	482.6	---	368.3	131.8	120.7	60.33	114.3	15.88	76.2	691
445T	1133.3	209.6	482.6	419.1	---	227.1	215.9	85.72	209.6	22.22	174.8	784
445TS	1038.4	209.6	482.6	419.1	---	131.8	120.7	60.33	114.3	15.88	76.2	777

(1)

(1) SPECIAL DIMENSIONS APPLYING TO THIS ORDER ON THIS LINE.

(2) "D" VARIES — 250T — 320T +0, -8.

(2) "D" VARIES — 360T — 440T +0, -1.5.

(3) "U" VARIES — UP TO 41.27 DIA. +0.00, -0.03

(3) "U" VARIES — 41.27 AND LARGER +0.00, -0.03

(4) ALL FRAMES HAVE EIGHT MOUNTING HOLES FOR DUAL MOUNTING.

(5) MOTOR WEIGHTS MAY VARY BY 15% DEPENDING UPON RATING.

(6) "N-W" VARIES +0, -6.4.

(7) DIMENSIONS ARE IN INCHES.

FRAME-_____TYPE-_____CERTIFIED FOR-_____

ORDER-_____ITEM-_____HP-_____RPM-_____PH-_____HZ-_____VOLTS-_____

RELANCE SALES ORDER-_____APPROVED BY-_____DATE-_____

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.

REV. DESC: UPDATE TITLE

REV. LTR: B

VERSION: 02

TDR: 000000498266

FILE: \RAG\00000\168

REVISED: 14:03:30 04/28/2009

MTL: -

BY: RAGEC

Baldor • Dodge • Reliance

DIM SHEET 250T THRU 440T METRIC

SH 1 of 1