


BALDOR

SH 1 of 1

[illegible]

DIMENSIONS ARE IN INCHES

					X T	LEAD CONNECTION			B.E.	KEY
						X	Y	XD	SQ.	LGTH.
FRAME BB	BD (2)	BE	BF							
.25	20.25	1.12	.69		1-1/2-13 - 8		1.25	10.88	.50	3.00
L360TY .25	20.25	1.12	.69		1-1/2-12 3 - 8		1.25	10.88	.50	3.00

- 1.) SPECIAL DIMENSIONS APPLYING TO THIS ORDER ON THIS LINE.
- 2.) "B" VARIES +.010.
- 3.) "U" VARIES +.0000, -.0005.
- 4.) "AK" VARIES +.001, -.002
- 5.) LEAD WIRE LENGTH AS SPECIFIED ON SALES ORDER.
- 6.) MINIMUM SUBMERGED DEPTH

FACE RUNOUT AND ECCENTRICITY .008 MAX. T.I.R.
PROTECTIVE CONDUIT FURNISHED BY CUSTOMER.