



35LYX145

35LYX145

510-520 = 16.25
520-528 = 17.25
529-535 = 18.12
536-546 = 19.50

1 HOLE
.41 DIA.
KNOCK OUT

2 HOLES
.88 DIA
KNOCK OUT

BRAKE RELEASE
TWO LEVERS
180° APART

3 THRU 15 FT-LB
BRAKE ONLY

BRAKE
LEADS

NAMEPLATE

.19 KEY
1.38 LONG

Ø 6.49

Ø 4.500

Ø .6250
Ø .6245

LEAD HOLE
Ø1.12 W/PLUG
(EACH SIDE)

4 HOLES
.38-16 TAP
ON 5.88
DIA. B.C.

SNAP RING

FRONT END DETAIL

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: CHANGE 35GS3009 TO 35GS3023, FIX KOBX MOUNT LOC			
REV: F	VERSION: 06	REVISED: 10:48:11 10/20/2023	TDR: 000001211789
MODEL NO. 35LYX145			REF: -
BY: ENFRAJ0			B

BALDOR - RELIANCE®

VERT 56C TEFC M F3 W/DODGE 'D' SERIES BRAKE & 35CB4007
SH 1 of 1