

ABB BALDOR RELIANCE III

Customer information packet

VEM3156T

1HP, 1170RPM, 3PH, 60HZ, 145TC, 3526M, ODP, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	ODP
Frame	145TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CURUSEEV NEMA PREMIUM
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	3.000 A @ 230.0 V 1.500 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	82.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.5 a
Insulation Class	F

Part Detail

Revision	F
Type	AC
Mech. spec.	35Z413
Base	
Status	PRD/A
Elec. spec.	35WGG019
Layout	35LYZ413
Eff. date	01-08-2026
CD Diagram	CD0005
Poles	06
Leads	9#18 Y
Proprietary	False
Created date	09-09-2022

Inverter Code	Inverter Ready
KVA Code	J
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3526M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	13.25 IN
Power Factor	67
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1170 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1259LUA									
CAT.NO.	VEM3156T								
SPEC.	35Z413G019G1								
HP	1								
VOLTS	230/460								
AMPS	3/1.5								
R.P.M.	1170								
FRAME	145TC	HZ		60	PH		3		
SER.F.	1.15	CODE	J	DES	B	CLASS	F		
NEMA NOM. EFF.	82.5	P.F.		67					
RATING	40C AMB-CONT								
CC	010A								
DE	6205	ODE		6203					
ENCL	ODP	SN							
USABLE AT	N/A								

AC Induction Motor Performance Data

Record # 82288

Typical performance - not guaranteed values

Winding: 35WGG019-R003			Type: 3526M		Enclosure: OPEN			
Nameplate Data				460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		1	Full Load Torque		4.479 LB-FT			
Volts		230/460	Start Configuration		direct on line			
Full Load Amps		3.0/1.5	Breakdown Torque		11.9 LB-FT			
R.P.M.		1155	Pull-up Torque		7.06 LB-FT			
Hz	60	Phase	3	Locked-rotor Torque		8.62 LB-FT		
NEMA Design Code		B	KVA Code	J	Starting Current		9.06 A	
Service Factor (S.F.)		1.15	No-load Current		1.02 A			
NEMA Nom. Eff.		0	Power Factor		0	Line-line Res. @ 25°C		20.372 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		46°C	
S.F. Amps			Temp. Rise @ S.F. Load		56°C			
			Locked-rotor Power Factor		48			

Load Characteristics 460 V, 60 Hz, 1 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	29	47	1	1	1	1	1
Efficiency	73.5	81.9	83.5	83.1	81.6	79.1	82.2
Speed	1192.5	1185.4	1177.6	1168.7	1159	1147	1163
Line amperes	1.07	1.21	1.41	1.67	1.98	2.35	1.86

ABB Motors and Mechanical Inc.

WINDING # 35WGG019

Typical performance - not guaranteed values.

1 HP 3 PH 60 HZ 1155 RPM 460 V 3526M

TORQUES (LB-FT): PO=11.9 PU=7.06 LR=8.62 LRA=9.06





