



35LYE016

510-520 = 11.12  
 521-528 = 12.12  
 529-535 = 12.99  
 536-546 = 14.37

NAMEPLATE

.19 KEY  
 1.38 LONG

0

Ø 4.500  
 4.497

Ø .8750  
 .8745

Ø 6.49

2.59

2.12

.13

.13

Ø 6.61

45°

45°

LEAD HOLE  
 Ø .88

4 HOLES  
 .38-16 TAP  
 ON Ø 5.88 B.C.

4.63

5.74

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: UPDATE 3D MODEL BOM PER REV W, NO CHG TO 2D PRINT			
REV: R	VERSION: 08	REVISED: 02:32:46 03/16/2022	TDR: 000001187751
MODEL NO. 35LYE016			REF: -
BY: USBUFRA			<b>B</b>

**BALDOR - RELIANCE®**

STD VERT 143-5TC TENV 35M  
 SH 1 of 1

35LYE016