

DUTY MASTER ALTERNATING CURRENT MOTORS

SQUIRREL-CAGE INDUCTION





ENCLOSURE: TOTALLY ENCLOSED

FRAME G447TS
INCLUDES G445TS FRAME MOUNTING HOLES

COOLING: FAN COOLED

MOUNTING: FOOT, F-1 SIDE

STEEL MAIN CONDUIT BOX



1 OBSTRUCTION MUST NOT ENCROACH ON AIR INLET.

IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.

DIMENSIONS ARE IN INCHES.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

REV. DESC: NEW			
REV: -	VERSION: 00	REVISED: 02:52:53 02/23/2018	TDR: 00000106199
MODEL NO. 617434-383			REF:
BY: RAGBXN		Material:	

BALDOR

G447TS - TEFC - FT - F1 - STEEL CBOX - AIR DEFLECTOR

MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT
EXTENSION IS .003" T.I.R. TO 5" DIA.