

Super White Washdown Duty Motors 1-20 Hp 56C thru 256TC



**NEMA
Premium**

Applications:

Food and beverage processing plants. Specially designed for humid and moist environments where motors receive sanitary washdowns on a regular basis.

Features:

- Labyrinth seal on each end of motor protects bearings by rotating and expelling contaminants
- Same size, sealed ball bearings on each end
- Moisture resistant insulation system
- Autophoretic[®] autodeposition surface preparation method makes white epoxy finish coat five times more resistant to corrosion and chipping than previous methods.
- Easily removable condensation drain plugs
- 300 series stainless steel shaft, hardware and nameplate
- Enhanced sealing around lead exit
- Inverter Ready
- Mobil Polyrex[®]EM moisture resistant grease
- Super-E[®] with NEMA Premium efficiency and 3-year product warranty

BALDOR[®]

A MEMBER OF THE ABB GROUP

Super White Washdown Duty Motors

Three Phase, TEFC, C-Face, Foot Mounted

Hp	kW	RPM	NEMA Frame	Catalog Number	List Price	Mult. Sym.	"C" Dim.	Aprx. Wt. (lb)	Full Load Efficiency	Bearing Size Ea. End	Voltage	Full Load Amps
1	0.75	3600	56C	CEWWDM3545	1,112	WD	12.35	34	77	6205	230/460	1.4
		1800	56C	CEFWWDM3546	1,146	WD	12.35	37	85.5	6205	208-230/460	1.5
		1800	143TC	CEFWWDM3546T	1,170	WD	13.28	38	85.5	6205	208-230/460	1.5
1.5	1.1	3600	56C	CEFWWDM3550	1,230	WD	13.35	46	85.5	6205	208-230/460	2
		1800	145TC	CEFWWDM3554T	1,253	WD	13.28	43	86.5	6205	208-230/460	2.2
2	1.5	3600	56HCY	CEWWDM3555	1,236	WD	13.32	41	85.5	6205	208-230/460	2.5
		3600	145TC	CEWWDM3555T	1,261	WD	13.28	41	85.5	6205	208-230/460	2.5
		1800	145TC	CEWWDM3558T	1,316	WD	13.28	48	86.5	6205	208-230/460	2.9
3	2.2	3600	145TC	CEWWDM3559T	1,553	WD	14.17	61	86.5	6205	230/460	3.6
		3600	182TC	CEWWDM3610T	1,464	WD	16.54	75	88.5	6206	208-230/460	3.4
		1800	182TC	CEWWDM3611T	1,727	WD	16.54	81	89.5	6206	208-230/460	4.2
5	3.7	3600	184TC	CEWWDM3613T	2,055	WD	16.54	83	88.5	6206	208-230/460	5.9
		1800	184TC	CEWWDM3615T	1,958	WD	18.04	97	89.5	6206	208-230/460	6.7
7.5	5.6	3600	184TC	CEWWDM3616T	2,442	WD	18.04	104	89.5	6206	208-230/460	8.4
		3600	213TC	CEWWDM3709T	2,895	WD	18.64	121	89.5	6307	208-230/460	9
		1800	213TC	CEWWDM3710T	2,476	WD	19.78	127	91.7	6307	230/460	9.4
10	7.5	3600	215TC	CEWWDM3711T	3,186	WD	18.64	118	90.2	6307	208-230/460	11.8
		1800	215TC	CEWWDM3714T	2,815	WD	21.27	165	91.7	6307	230/460	12
15	11	3600	215TC	CEWWDM3713T	4,003	WD	21.26	169	91	6307	208-230/460	17
		3600	254TC	CEWWDM23994T	5,623	WD	23.57	240	91	6309	230/460	16.7
		1800	254TC	CEWWDM23933T	5,535	WD	23.57	255	92.4	6309	230/460	18
20	15	3600	256TC	CEWWDM41906T	6,454	WD	23.57	260	91	6309	230/460	23
		1800	256TC	CEWWDM23934T	6,418	WD	23.57	286	93	6309	208-230/460	24

For additional information on these or any other Baldor products, please visit www.baldor.com or contact your local Baldor•Reliance Sales Representative.



Baldor Electric Company
P.O. Box 2400 • Fort Smith, AR 72902-2400 U.S.A.
Phone (479) 646-4711 • Fax (479) 648-5792