


APG Rebuild Kits

Rebuild Kits consist of all high wear internal components that are routinely replaced when servicing a reducer: bearing kit, seal kit, shim kit and factory approved gear lubricant. APG Rebuild Kits are for C-Face units only and include the bearing for the motor adapter.



Features

Rebuild kits provide several benefits when stocked as parts at a user location:

- Protection from excessive down time that can occur following unexpected equipment shut-down
- Parts on hand for routine scheduled maintenance
- Boxed kit may be identified to a specific machine; no more searching for individual components
- Kits contain only genuine Dodge renewal parts for optimum performance

SIZE	MOTOR FRAME	REBUILD KIT	C-FACE BRG	BEARING KIT	I/P SEAL	O/P SEAL	SHIM KIT	LUBRICANT	QTY
SM2	56C/140TC	60244122A	07914702AC	41164245AW	41162701CR	41162701DE	41164246Y	41170966AE	1 Quart
	180TC				41162701CS				
DM2	56C/140TC	60244122B	07914702AC	41164245AE	41162701GB	41162701FY	41164246DE	41170966AE	1 Quart
	180TC				41162701CS				
DM2F	56C/140TC	60244122C	07914702AC	41164245AX	41162701GB	41162701DF	41164246DE	41170966AE	1 Quart
	180TC				41162701CS				
TM2	56C/140TC	60244122D	07914702AC	41164245AM	41162701GB	41162701FY	41164246DF	41170966AE	1 Quart
	180TC				41162701CS				
TM2F	56C/140TC	60244122E	07914702AC	41164245AY	41162701GB	41162701DF	41164246DF	41170966AE	1 Quart
	180TC				41162701CS				
SM3	56C/140TC	60244122F	07914702CR	41164245Y	41162701CE	41162701GJ	41164246Z	41170966AE	1 Quart
	180TC/210TC	60244122G	07914702CS		41162701CF				
DM3	56C/140TC	60244122H	07914702CR	41164245AF	41162701CE	41162701GA	41164246DG	41170966AE	2 Quarts
	180TC/210TC	60244122J	07914702CS		41162701CF				
TM3	56C/140TC	60244122K	07914702CR	41164245AN	41162701CE	41162701GA	41164246DH	41170966AE	2 Quarts
	180TC/210TC	60244122L	07914702CS		41162701CF				
SM4	56C/140TC	60244122M	07914702CR	41164245Z	41162701CE	41162701GJ	41164246Z	41170966AE	1 Quart
	180/210/250TC	60244122N	07914702CS		41162701CF				
DM4	56C/140TC	60244122P	07914702CR	41164245AG	41162701CE	41162701GB	41164246DJ	41170966AE	2 Quarts
	180/210/250TC	60244122R	07914702CS		41162701CF				
DM4F	56C/140TC	60244122S	07914702CR	41164245AZ	41162701CE	41162701CX	41164246ET	41170966AE	2 Quarts
	180/210/250TC	60244122T	07914702CS		41162701CF				
TM4	56C/140TC	60244122U	07914702CR	41164245AP	41162701CE	41162701GB	41164246DK	41170966AE	2 Quarts
	180/210/250TC	60244122W	07914702CS		41162701CF				
TM4F	56C/140TC	60244122X	07914702CR	41164245BA	41162701CE	41162701CX	41164246EU	41170966AE	2 Quarts
	180/210/250TC	60244122Y	07914702CS		41162701CF				

SIZE	MOTOR FRAME	REBUILD KIT	C-FACE BRG	BEARING KIT	I/P SEAL	O/P SEAL	SHIM KIT	LUBRICANT	QTY
SM5	56C/140TC	60244122Z	07914702CR	41164245AA	41162701CE	41162701GK	41164246N	41170966AE	2 Quarts
	180/210TC	60244122AA	07914702CS		41162701CF				
	250TC	60244122AB	07914702CT		41162701CG				
	280TC	60244122AC	07914702CM						
DM5	56/140TC	60244122AD	07914702CR	41164245AH	41162701CE	41162701GC	41164246DL	41170966AF	1 Gallon
	180/210TC	60244122AE	07914702CS		41162701CF				
	250TC	60244122AF	07914702CT		41162701CG				
	280TC	60244122AG	07914702CM						
TM5	56/140TC	60244122AH	07914702CR	41164245AR	41162701CE	41162701GC	41164246DM	41170966AF	1 Gallon
	180/210TC	60244122AJ	07914702CS		41162701CF				
	250TC	60244122AK	07914702CT		41162701CG				
	280TC	60244122AL	07914702CM						
SM6	140TC	60244122AM	07914702CR	41164246AB	41162701CE	41162701GL	41164246H	41170966AE	3 Quarts
	180/210TC	60244122AN	07914702CS		41162701CF				
	250TC	60244122AP	07914702CT		41162701CG				
	280TC	60244122AR	07914702CM		41162701CH				
DM6	140TC	60244122AT	07914702CR	41164245AJ	41162701CE	41162701GD	41164246DN	41170966AE 41170966AF	1 Quart 1 Gallon
	180/210TC	60244122AU	07914702CS		41162701CF				
	250TC	60244122AW	07914702CT		41162701CG				
	280TC	60244122AX	07914702CM		41162701CH				
TM6	140TC	60244122AZ	07914702CR	41164245AS	41162701CE	41162701GD	41164246DP	41170966AE 41170966AF	1 Quart 1 Gallon
	180/210TC	60244122BA	07914702CS		41162701CF				
	250TC	60244122BB	07914702CT		41162701CG				
	280TC	60244122BC	07914702CM		41162701CH				
SM7	180/210TC	60244122BE	07914702CS	41164245AC	41162701CF	41162701GD	41164246V	41170966AF	2 Gallons
	250TC	60244122BF	07914702CT		41162701CG				
	280TC	60244122BG	07914702CM		41162701CH				
	320/360TC	60244122BH	07914703CP		41162701CJ				
DM7	180/210TC	60244122BK	07914702CS	41164245AK	41162701CF	41162701GE	41164246DR	41170966AF	4 Gallons
	250TC	60244122BL	07914702CT		41162701CG				
	280TC	60244122BM	07914702CM		41162701CH				
	320/360TC	60244122BN	07914703CP		41162701CJ				
TM7	180/210TC	60244122BR	07914702CS	41164245AT	41162701CF	41162701GE	41164246DS	41170966AE 41170966AF	1 Quart 4 Gallons
	250TC	60244122BS	07914702CT		41162701CG				
	280TC	60244122BT	07914702CM		41162701CH				
	320/360TC	60244122BU	07914703CP		41162701CJ				
SM8	180/210TC	60244122BX	07914702CS	41164245AD	41162701CF	41162701GE	41164246W	41170966AE 41170966AF	1 Quart 1 Gallon
	250TC	60244122BY	07914702CT		41162701CG				
	280TC	60244122BZ	07914702CM		41162701CH				
	320/360TC	60244122CA	07914703CP		41162701CJ				
DM8	180/210TC	60244122CC	07914702CS	41164245AL	41162701CF	41162701GF	41164246DW	41170966AF	4 Gallons
	250TC	60244122CD	07914702CT		41162701CG				
	280TC	60244122CE	07914702CM		41162701CH				
	320/360TC	60244122CF	07914703CP		41162701CJ				
TM8	180/210TC	60244122CH	07914702CS	41164245AV	41162701CF	41162701GF	41164246DX	41170966AE 41170966AF	2 Quarts 4 Gallons
	250TC	60244122CJ	07914702CT		41162701CG				
	280TC	60244122CK	07914702CM		41162701CH				
	320/360TC	60244122CL	07914703CP		41162701CJ				
400TC	60244122CM	07914703CN							



World Headquarters

P.O. Box 2400, Fort Smith, AR 72902-2400 U.S.A., Ph: (1) 479.646.4711, Fax (1) 479.648.5792, International Fax (1) 479.648.5895

Baldor - Dodge

6040 Ponders Court, Greenville, SC 29615-4617 U.S.A., Ph: (1) 864.297.4800, Fax: (1) 864.281.2433

www.baldor.com