



BALDOR GENERATORS

GENERAL INSTALLATION
FOR IDLC GENERATORS


UL2200 MODEL#	MODEL#	OVERALL LENGTH L	OVERALL WIDTH W	OVERALL HEIGHT H	HOOD LENGTH HL	BASE WIDTH BW	MOUNTING HOLE 1 M1	MOUNTING HOLE 2 M2	MOUNTING WIDTH MW	TANK HEIGHT TH (12-17 HRS)	TANK HEIGHT TH (24-34 HRS)	TANK HEIGHT TH (FRAME ONLY)
IDLC30-3JU	IDLC30-3J	132	63	78	36	54	18.00	62.00	51.00	8	14	6
IDLC40-3JU	IDLC40-3J			79				74.00				
IDLC50-3JU	IDLC50-3J			91				82.00				
IDLC60-3JU	IDLC60-3J			92				94.00				
IDLC80-3JU	IDLC80-3J	153	63	91	36	54	22.00	82.00	51.00	11	14	6
IDLC100-3JU	IDLC100-3J			92				94.00				
IDLC125-3JU	IDLC125-3J			92				94.00				
IDLC150-3JU	IDLC150-3J	153	63	92	36	54	22.00	94.00	51.00	11	14	6




PLAN VIEW




REAR VIEW




PLAN VIEW OF TANK ONLY



RIGHT SIDE VIEW



FRONT VIEW



LEFT SIDE VIEW

NOTES:

FOR PRODUCT DATA REFER TO BALDOR MODEL SPEC SHEETS

FOR INSTALLATION RECOMMENDATIONS REFER TO GEN SET MANUAL MN2407

ALL DIMENSIONS IN INCHES

DRAWING TO SCALE

TOLERANCES UNLESS OTHERWISE SPECIFIED
DECIMALS .XX ±.25 FRACTIONS ±1/4

(4) Ø.75 MTG. HOLES

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.

REV. DESC: UPDATE TIER ON 30-60		
REV. LTR: F	VERSION: 06	TDR: 000000528793
FILE: \PGA\00010\468	REVISED: 08:29:57 03/09/2010	BY: PGCONBO
MTL: -	TAB: SA_L1_30_150	

BALDOR • DODGE • RELIANCE

IDLC 30-500-07E

SH 9 of 12