

**BALDOR • RELIANCE**

---

# Customer information packet

## 1215W

2HP, 1500/1800RPM, 3PH, 50/60HZ, 3628M, GRND

**Specifications**

<b>Frequency</b>	50.00 Hz
	60.00 Hz
<b>Nameplate Output</b>	2
<b>Number of Poles</b>	4
<b>Phase</b>	3
<b>Product Style</b>	GRINDER
<b>Speed</b>	1500 rpm
	1800 rpm
<b>Voltage</b>	208 V
	230 V
	460 V

**Part detail**


<b>Revision</b>	S
<b>Type</b>	AC
<b>Mech. spec.</b>	G12-118
<b>Base</b>	
<b>Status</b>	PRD/A
<b>Elec. spec.</b>	G2WG0018
<b>Layout</b>	G2LY0118
<b>Eff. date</b>	12-15-2021
<b>CD Diagram</b>	CD0251
<b>Poles</b>	04
<b>Leads</b>	9#16 12"FRM STAT IRN Y
<b>Proprietary</b>	False
<b>Created date</b>	01-01-0001

**Nameplate**


<b>NP3412L</b>			
<b>CAT.NO.</b>	1215W		
<b>HP</b>	2	<b>VOLTS</b>	208-230/460
<b>PHASE</b>	3	<b>AMPS</b>	5.9-5.6/2.8
<b>HZ</b>	50//60	<b>RPM</b>	1500//1800
<b>SER.NO</b>			
<b>SPEC.</b>	G12-118D-0018		
<b>BLANK</b>			

**Accessories**

<b>Part number</b>	<b>Description</b>	<b>Multiplier</b>
GA20	PEDESTAL INDUSTRIAL, CAST IRON 8"-14"	A8
GA9	PAIR LIGHTED EYESHIELDS	A8
GA9-1	SINGLE LIGHTED EYESHIELD	A8
GA9S	PAIR EYESHIELDS W/ ON-OFF SWITCH	A8
GA11	PAIR EYESHIELDS	A8
B125	12" 30 GRIT GRINDING WHEEL	A8
B126	12" 46 GRIT GRINDING WHEEL	A8
DC12	DUST CONTROL UNIT	A8
DC12-3	DUST CONTROL UNIT	A8



CD0251



CD0251

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: C	BY: EAH	REVISED: 05/05/99 10:07	TDR: 0179909
CD0251		FILE: AAA00051265	MDL: -
		MTL: -	

**BALDOR ELECTRIC Co.**

3PH, DV, 9 LEAD, GRINDER OR BUFFER W/MANUAL STARTER

