





NOTE:

1. SHAFT RUNOUT ON BOTH ENDS
(2.25" FROM END OF SHAFT)
MUST BE .002 MAX. T.I.R.



CUST. NAME		CUST. P.O.		CERTIFIED BY		MODEL		INSUL		AMB		
H.P.	MTG	TYPE	R.P.M.	VOLTS		ENCL	PHASE	FREQ	FRAME			
REV. DESC: MOVED STARTER BOX TO CENTER OF MOTOR						BALDOR ELECTRIC Co.						
REV. LTR: A		BY: JD	REVISED: 01/07/00 2:15		TDR: 0199019							
FILE: AAA00066298				MDL: --								
MTL: --												
						STD 14" BUFFER 37 FRAME W/ 'GE' MAGNETIC STARTER						