

BALDOR® • RELIANCE™

Customer information packet

1022WD

28C 4P GRNDR W/EXH

Specifications

Frequency	60.00 Hz
Nameplate Output	1
Number of Poles	4
Phase	1
Product Style	GRINDER
Shaft Diameter	0.875 IN
Speed	1800 rpm
Voltage	115 V 230 V

Part detail

Revision	AZ
Type	AC
Mech. spec.	G10-237
Base	
Status	PRD/A
Elec. spec.	G0WG0002
Layout	G0LY0237
Eff. date	08-23-2022
CD Diagram	CD0279
Poles	04
Leads	4#18 SEE NOTES Y
Proprietary	False
Created date	01-01-0001

Nameplate

NP3118			
CAT.NO.	1022WD		
HP	1	VOLTS	115/230
PHASE	1	AMPS	5.4/2.7
HZ	60	RPM	1800
SER.NO			
SPEC.	G10-237-2		

Accessories

Part number	Description	Multiplier
GA16	PEDESTAL INDUSTRIAL, CAST IRON 6" - 10"	A8
GA14	PEDESTAL FABRICATED STEEL W/SHELVES	A8
GA20	PEDESTAL INDUSTRIAL, CAST IRON 8"-14"	A8
GA20E	PEDESTAL LIGHT INDUSTRIAL,STEEL	A8
B102	10" 36 GRIT GRINDING WHEEL	A8
B103	10" 60 GRIT GRINDING WHEEL	A8
GA9	PAIR LIGHTED EYESHIELDS	A8
GA9-1	SINGLE LIGHTED EYESHIELD	A8
GA9S	PAIR EYESHIELDS W/ ON-OFF SWITCH	A8
GA11	PAIR EYESHIELDS	A8
DC10	DUST CONTROL UNIT	A8
BQ1-015-CC	1PH Brake, NEMA 1,110-125 VAC, 50/60Hz	
BQ1-015-CP	1PH Brake, Panel 110-125 VAC, 50/60 Hz	P1
BQ2-015-CC	1PH Brake,NEMA 1 208-230 VAC,50/60Hz	
BQ2-015-CP	1PH Brake, Panel 208-230 VAC, 50/60 Hz	



