



Customer information packet

AEM4307-4

40HP, 1780RPM, 3PH, 60HZ, 364U, 1448M, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	364U
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	40.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	CSA EEV CCSA US
Ambient Temperature	65 °C
Auxillary Box	No Auxillary Box
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Current @ Voltage	45.000 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	94.5 %
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	45.0 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	G
Lifting Lugs	No Lifting Lugs
Motor Lead Quantity/Wire Size	3 @ 6 AWG
Motor Standards	NEMA
Motor Type	A36050M

Part detail


Revision	J
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A36WG0744
Layout	617428-014
Eff. date	11-06-2020
CD Diagram	416820-036
Poles	04
Leads	3#6
Proprietary	False
Created date	10-19-2010

Mounting Arrangement	F1
Number of Poles	4
Overall Length	33.94 IN
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Service Factor	1.00
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1785 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate


NP2492L

SPEC NO.	P36G3112			CAT.NO.	AEM4307-4			FRAME	364U
HP	40	VOLTS	460	PHASE	3	DESIGN	B	TYPE	P
RPM	1785	AMPS	45	HZ	60	AMB	65	SF	1.00
DRIVE END BEARING	65BC03JPP30A			LUBRICATION	DUTY	CONT	INSUL.CLASS F		
OPP D.E. BEARING	65BC03JPP30A			MOBIL POLYREX EM		ENCL	TEFC	CODE	G
AMB	ALERNATE RATING-S.F.		ALTITUDE		NEMA-NOM-EFF		94.5		
65	1.00	3300	GUARANTEED EFFICIENCY		93.6				
SER.NO.				CAT# AEM4307-4					
MOTOR WEIGHT		884							



416820-036

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 3 LEAD CONNECTED



(N.P. 1575-BA)

416820-036

REV. DESC: LOADED TO BUS, C/R 335225		
REV. LTR: -	VERSION: 00	TDR: 000000538207
FILE: \MGA\00000\682	REVISED: 11:54:06 04/30/2010	
MTL: -	BY: RAGRA	

BALDOR

CONN DIAG - STANDARD 3 LEAD
SH 1 of 1