

ABB BALDOR RELIANCE III

Customer information packet

AEM3687-4

1.5HP, 1170RPM, 3PH, 60HZ, 184, 0630M, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	184
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	UR CSA
Ambient Temperature	65 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	2.500 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	87.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	2.5 a
Insulation Class	F
Inverter Code	Inverter Ready

Part Detail

Revision	H
Type	AC
Mech. spec.	06F062
Base	
Status	PRD/A
Elec. spec.	06WGX235
Layout	06LYF062
Eff. date	03-05-2026
CD Diagram	CD0006
Poles	06
Leads	3#16
Proprietary	False
Created date	02-23-2015

IP Rating	NONE
KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0630M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	14.74 IN
Power Factor	64
Product Family	Automotive (Not For DC)
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	0.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1170 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1404									
CAT.NO.									
SPEC.	06F062X235G1								
VOLTS	460								
AMP	2.5								
RPM	1170			HP	1.5				
FRAME	184		HZ	60		PH	3		
SER.F.	1.00		CODE	K		DES	B	CL	F
NEMA-NOM-EFF	87.5		PF	64					
G.MIN.EFF	85.5		CC	010A					
RATING	65C AMB-CONT								
LUBRICATION	POLYREX EM								
DE	6206		ODE	6205					
ENCL	TEFC		SER. #						

Accessories

Part number	Description	Multiplier
36-1037	C FACE KIT	A8

AC Induction Motor Performance Data

Record # 49368

Typical performance - not guaranteed values

Winding: 06WGX235-R019			Type: 0630M		Enclosure: TEFC			
Nameplate Data			460 V, 60 Hz: Single Voltage Motor					
Rated Output (HP)		1.5	Full Load Torque		6.77 LB-FT			
Volts		460	Start Configuration		direct on line			
Full Load Amps		2.5	Breakdown Torque		24 LB-FT			
R.P.M.		1170	Pull-up Torque		12.5 LB-FT			
Hz		60	Phase		3	Locked-rotor Torque	15.8 LB-FT	
NEMA Design Code		B	KVA Code		K	Starting Current	16.2 A	
Service Factor (S.F.)			1	No-load Current		1.63 A		
NEMA Nom. Eff.		87.5	Power Factor		64	Line-line Res. @ 25°C		7.01 Ω
Rating - Duty		65C AMB-CONT		Temp. Rise @ Rated Load		26°C		
				Locked-rotor Power Factor		30.4		
				Rotor inertia		0.282 LB-FT2		

Load Characteristics 460 V, 60 Hz, 1.5 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	27	44	56	64	69	73
Efficiency	76.3	84.8	86.9	87.6	87.1	85.9
Speed	1194	1187	1179	1172	1163	1153
Line amperes	1.7	1.9	2.18	2.51	2.92	3.38


ABB Motors and Mechanical Inc.

WINDING # 06WGX235

Typical performance - not guaranteed values.



1.5 HP 3 PH 60 HZ 1170 RPM 460 V 0630M

TORQUES (LB-FT): PO=24 PU=12.5 LR=15.8 LRA=16.2





CD0006


NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007

REV. LTR: E

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\141

REVISED: 10:24:49 02/19/2019

BY: ENBRIRO

MTL: —


BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1