ABB BALDOR RELIANCE

Customer information packet

AEM4311-4

50HP, 1780RPM, 3PH, 60HZ, 365U, 1458M, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/18/2026 4:06:59 AM

Specifications

Enclosure	TEFC
Frame	365U
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	50.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	CSA EEV
	CCSA US
Ambient Temperature	65 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Current @ Voltage	56.000 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	94.5 %
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	56.0 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	G
Lifting Lugs	No Lifting Lugs
Motor Lead Quantity/Wire Size	3 @ 4 AWG
Motor Standards	NEMA
Motor Type	A36062M

Part Detail

Revision	D
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A36WG4089
Layout	617428-014
Eff. date	07-24-2025
CD Diagram	CD0006
Poles	04
Leads	3#4
Proprietary	False
Created date	07-21-2016

Mounting Arrangement	F1
Number of Poles	4
Overall Length	33.94 IN
Power Factor	88
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Service Factor	1.00
Shaft Diameter	2.124 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1780 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate

NP2492L												
SPEC NO.	P36G3114			**CAT.NO.**	AEM4311-4					**FRAME**	365U	
HP	50	**VOLTS**	460	**PHASE**	3	**DESIGN**	B	**TYPE**	P			
RPM	1780	**AMPS**	58	**HZ**	60	**AMB**	65	**SF**	1.00			
DRIVE END BEARING	65BC03JPP30A			**LUBRICATION**		**DUTY**	CONT			**INSUL.CLASS**	F	
OPP D.E. BEARING	65BC03JPP30A			**MOBIL POLYREX EM**		**ENCL**	TEFC	**CODE**	G			
AMB	**ALERNATE RATING-S.F.**			**ALTITUDE**				**NEMA-NOM-EFF**		94.5		
65	**1.00**		**3300**	**GUARANTEED EFFICIENCY**			93.6					
SER.NO.												
	MOTOR WEIGHT											

DUTY MASTER ALTERNATING CURRENT MOTORS


SQUIRREL-CAGE INDUCTION
CAST IRON CONSTRUCTION

ENCLOSURE: TOTALLY ENCLOSED
MOUNTING: FOOT

FRAMES 364U-365U

COOLING: FAN COOLED

617428-014



MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STD. SHAFT EXTNESION IS .002 T.I.R. UP TO AND INCLUDING 1.625 DIA. AND .003 T.I.R. 1.625 DIA. TO 5 INCH DIA.

WEIGHT (LBS): 364U = 865
365U = 890

MOTOR WEIGHTS MAY VARY BY 15% DEPENDING UPON RATING.

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: CHG SHAFT TO MEET "BA' REQUIREMENT OF 5.88			
REV: B	VERSION: 02	REVISED: 10:58:41 05/31/2017	TDR: 000000983755
MODEL NO. 617428-014			REF:
BY: RAGGDM			B


BALDOR


DIM SHT 364-365U, SINGLE EXT XT (611740-531)

617428-014


CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1