ABB BALDOR RELIANCE

Customer information packet

AM2276-4

7.5HP, 1170RPM, 3PH, 60HZ, 256U, 0946M, TEFC
Class -
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/19/2026 11:43:38 AM

Specifications

Enclosure	TEFC
Frame	256U
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Division	Not Applicable
Output @ Frequency	7.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	CSA
	UR
Ambient Temperature	65 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	10.800 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	10.8 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	H
Lifting Lugs	Standard Lifting Lugs

Part Detail

Revision	E
Type	AC
Mech. spec.	09T36
Base	
Status	INA/A
Elec. spec.	09WGY654
Layout	09LYT036
Eff. date	10-06-2020
CD Diagram	CD0006
Poles	06
Leads	3#12
Proprietary	False
Created date	01-01-0001

Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 12 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0940M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	22.91 IN
Power Factor	73
Product Family	Automotive (Not For DC)
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1175 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor

Nameplate

NP1404									
CAT.NO.									
SPEC.	09T036Y654G1								
VOLTS	460								
AMP	10.8								
RPM	1175		**HP**	7.5					
FRAME	256U	**HZ**	60		**PH**	3			
SER.F.	1.00	**CODE**	H	**DES**	B	**CL**	F		
NEMA-NOM-EFF	89.5	**PF**	73						
G.MIN.EFF		**CC**							
RATING	65C AMB-CONT								
LUBRICATION	POLYREX EM								
DE	6309	**ODE**	6208						
ENCL	TEFC	**SER. #**							

Accessories

Part number	Description	Multiplier
09-1309	C FACE KIT	A8

AC Induction Motor Performance Data
Record # 20720
Typical performance - not guaranteed values

Winding: 09WGY654-R003	**Type:** 0940M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			7.5	**Full Load Torque**	33.5 LB-FT
Volts			460	**Start Configuration**	direct on line
Full Load Amps			10.8	**Breakdown Torque**	85.7 LB-FT
R.P.M.			1175	**Pull-up Torque**	37.7 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	52.1 LB-FT
NEMA Design Code	B	**KVA Code**	H	**Starting Current**	59.7 A
Service Factor (S.F.)			1	**No-load Current**	5.15 A
NEMA Nom. Eff.	89.5	**Power Factor**	73	**Line-line Res. @ 25ºC**	1.19 Ω
Rating - Duty			65C AMB-CONT	**Temp. Rise @ Rated Load**	42°C
				Locked-rotor Power Factor	26
				Rotor inertia	3.21 LB-FT2

Load Characteristics 460 V, 60 Hz, 7.5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	37	57	67	73	75	74	74
Efficiency	82.4	88.6	89.7	89.5	88.6	87.1	89
Speed	1195	1190	1184	1177	1170	1161	1173
Line amperes	5.76	6.97	8.75	10.8	13.3	16.27	12.3


ABB Motors and Mechanical Inc.

WINDING # 09WGY654


7.5 HP 3 PH 60 HZ 1175 RPM 460 V 0940M

Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=85.7 PU=37.7 LR=52.1 LRA=59.7





11/19/2026 ACPERF, record # 20720


09LYT036
(920 - 960)
23.11
10.11
4.07
3.75
.31 KEY
2.75 LONG
Ø 1.3750
1.3745
SLINGER
(EA. END)
PLUG
(DRAIN)
DRAIN FITTING
(FR. END ONLY)
8.25
8.25
4.25
10.00
.75
11.50
12.94
10.32
6.63
2.70
12.88
6.25
6.19
3.27
.79
8 HOLES
Ø .53
LEAD HOLE
1.25 NPT
5.00
5.00
8.27
5.75
11.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: ADDED FEET DIMS IN RIGHT VIEW
REV: R
VERSION: 09
REVISED: 09:16:02 11/03/2026
TDR: 000001286748
MODEL NO. 09LYT036
REF: -
BY: ENSHAB0
B
BALDOR - RELIANCE®
HOR TEFC 254-6U (GM SPECS)
09LYT036


CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1