ABB BALDOR RELIANCE

Customer information packet

ANFL3514M

1.5HP, 1750RPM, 1PH, 60HZ, 56YZ, 3532LC, TEFC
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/21/2026 1:51:07 AM

Specifications

Enclosure	TEFC
Frame	56YZ
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	1.500 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	115.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	C UR US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	13.000 A @ 115.0 V
	6.500 A @ 230.0 V
	7.100 A @ 208.0 V
Design Code	L
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	80.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	Multiple Flats
Heater Indicator	No Heater
High Voltage Full Load Amps	6.5 a
Insulation Class	F

Part Detail

Revision	A
Type	AC
Mech. spec.	35R216
Base	
Status	PRD/A
Elec. spec.	35WGZ997
Layout	35LYR216
Eff. date	01-09-2026
CD Diagram	CD0320
Poles	04
Leads	4#16 A&J,2#18 B PH,1#14 #4TH
Proprietary	False
Created date	11-14-2024

Inverter Code	Not Inverter
KVA Code	J
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Quantity/Wire Size	4 @ 16 AWG, A&J
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3532LC
Mounting Arrangement	F1
Number of Poles	4
Overall Length	14.43 IN
Power Factor	95
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Other
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1750 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	Manual Thermal Overload
Winding Thermal 1 Location	KO
Winding Thermal 2	None

Nameplate

NP1280L									
CAT.NO.	ANFL3514M								
SPEC.	35R216Z997								
HP	1.5								
VOLTS	115/230								
AMP	13/6.5								
RPM	1750								
FRAME	56YZ	**HZ**	60		**PH**	1			
SER.F.	1.00	**CODE**	J	**DES**	L	**CL**	F		
NEMA-NOM-EFF	80	**PF**	95						
RATING	40C AMB-CONT								
CC									
DE	6203	**ODE**	6203						
ENCL	TEFC	**SN**							

Accessories

Part number	Description	Multiplier
35-8762	C FACE KIT	A8
35EP1506A01SP	D-FLANGE KIT	A8

AC Induction Motor Performance Data
Record # 109371
Typical performance - not guaranteed values

Winding: 35WGZ997-R008	**Type:** 3532LC	**Enclosure:** TEFC

Nameplate Data				**115 V, 60 Hz: Low Voltage Connection**	
Rated Output (HP)			1.5	**Full Load Torque**	4.597 LB-FT
Volts			115/230	**Start Configuration**	direct on line
Full Load Amps			13/6.5	**Breakdown Torque**	11.5 LB-FT
R.P.M.			1750	**Pull-up Torque**	9.24 LB-FT
Hz	60	**Phase**	1	**Locked-rotor Torque**	11.6 LB-FT
NEMA Design Code	L	**KVA Code**	J	**Starting Current**	93.9 A
Service Factor (S.F.)			1	**No-load Current**	3.64 A
NEMA Nom. Eff.	80	**Power Factor**	95	**Line-line Res. @ 25ºC**	2.1749 Ω A Ph 1.8972 Ω B Ph
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	64°C

Load Characteristics 115 V, 60 Hz, 1.5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	78	89	93	95	95	95
Efficiency	64.7	76.4	80.1	80.5	79.1	75.6
Speed	1788.1	1776.5	1764.6	1750.3	1735.8	1712.2
Line amperes	4.97	7.32	9.99	13	16.1	20.2


ABB Motors and Mechanical Inc.


WINDING # 35WGZ997

1.5 HP 1 PH 60 HZ 1750 RPM 115 V 3532LC


Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=11.5 PU=9.24 LR=11.6 LRA=93.9




35LYR216
510-520 = 12.55
521-528 = 13.55
529-535 = 14.43
.52
2.06
.12
.19 KEY
1.38 LONG
Ø7.19
NAMEPLATE
Ø6.82
Ø6.375
6.372
Ø.6250
.6245
Ø.6250
.6245
3.76
.500
.480
ACROSS FLATS
(FLATS 180° APART)
Ø6.66
5.84
5.57
45°
MANUAL THERMAL
W/BOOT
LEAD HOLE
Ø.88
4.56
2 HOLES
Ø.38 ON
Ø7.25 B.C.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: LOADING OF SWD DWG FOR 2D TO 3D CONVERSION - PKG16
REV: C
VERSION: 03
REVISED: 11:49:11 02/01/2019
TDR: 000001098202
MODEL NO. 35LYR216
REF: -
BY: ENSTEK0
B
BALDOR - RELIANCE®
VER AUGER MTR 56YZ TEFC 35LC W/TORQ SW & GUARD, 1" MTO IN KO
SH 1 OF 1
35LYR216

CD0320



	LINE A	LINE B	JOIN	JOIN
HIGH STD	1,8	4	2,3,5	J
HIGH OPP	1,5	4	2,3,8	J
LOW STD	1,3,8	4	–	2,J,5
LOW OPP	1,3,5	4	–	2,J,8

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
3. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0320

REV. DESC: ADD INTERNAL CONNECTION TO HELP MANUFACTURING		
REV. LTR: G	VERSION: 01	TDR: 000000941594
FILE: \AAA\00007\422	REVISED: 02:21:00 08/28/2015	BY: ENALEMO
MTL: –		

BALDOR

TYPE LC, DV, REV, THERMAL, B PH AMPS THRU HTR HVC, 7 LEAD

SH 1 of 1